



# OptiFlood LED BVP506

## BVP506 ECO181-3S/657 I DM GR T35

OptiFlood LED, LED EconomyLine 18100 lm, Distribution medium

OptiFlood LED is a range of stylish, extremely efficient asymmetric floodlights that can be used to illuminate large areas. Designed around the latest LED technology, it offers significant energy and maintenance savings compared with conventional HID systems. Thanks to its highly efficient LEDGine area optics, it can be used for area lighting applications that have traditionally required HID-equivalent power levels. Integrated controls are available as an option, enabling additional energy savings. And LED upgrades can be easily incorporated, making this a truly future-proof solution. With its compact shape and aesthetically pleasing design, OptiFlood LED can be used in applications where design and appearance are just important as technical performance.

### Product data

General Information		
Lamp family code	ECO181 [LED EconomyLine 18100 lm]	example B10. Therefore, the median useful life (B50) value also represents the B10 value.
Light source replaceable	Yes	
Number of gear units	1 unit	
Driver included	Yes	
Photocell	-	
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for	
Light source engine type	LED	
Product family code	BVP506 [OptiFlood LED]	
Lighting Technology	LED	
Embedded control	-	
CE mark	Yes	
Warranty period	5 years	
Flammability mark	-	
ENEC mark	ENEC mark	

# OptiFlood LED BVP506

EU RoHS compliant	Yes
-------------------	-----

## Light Technical

Upward light output ratio	0
Luminous Flux	15,615 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	5700 K
Luminous Efficacy (rated) (Nom)	101 lm/W
Color rendering index (CRI)	70
Number of light sources	76
Light source color	757 cool white
Optical cover type	Clear glass
Luminaire light beam spread	73° x 26°
Optic type outdoor	Distribution medium

## Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Average CLO power consumption	[delete] W
End CLO power consumption	[delete] W
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	149 W
Power Factor (Fraction)	0.9
Connection	Screw connector
Cable	-
Number of products on MCB of 16 A type B	8

## Temperature

Ambient temperature range	-30 to +35 °C
---------------------------	---------------

## Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit regulating
Control interface	-
Constant light output	No

## Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Glass
Fixation material	Aluminum
Housing Color	Grey

Mounting device	-
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	730 mm
Overall width	460 mm
Overall height	176 mm
Effective projected area	0.1 m <sup>2</sup>
Dimensions (Height x Width x Depth)	176 x 460 x 730 mm

## Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Surge Protection (Common/Differential)	4/4 kV
Protection class IEC	Safety class I

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.33, 0.34) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 75000 h	7.5 %
Lumen maintenance at median useful life* 75000 h	L80

## Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable

## Product Data

Order product name	BVP506 ECO181-3S/657 I DM GR T35
Full product name	BVP506 ECO181-3S/657 I DM GR T35
Full product code	871829141834400
Order code	41834400
Material Nr. (12NC)	910925439410
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291418344
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291418344

# OptiFlood LED BVP506

## Dimensional drawing

