



# Iridium<sup>2</sup> LED Medium

## BGP352 GRN78-3S/740 DM AL GR T15

Iridium<sup>2</sup> LED Medium, LED GreenLine 7800 lm, 740 neutral white, Distribution medium, Grey

Iridium<sup>2</sup> is a family of road-lighting luminaires designed for performance and sustainability. Depending on the application and budget, customers can start with LED, electronic HID or a mix of both technologies with the same luminaire. Whatever the initial choice, Iridium<sup>2</sup>'s modularity allows customers to upgrade their installations (LED to LED or e-HID to LED) whenever they want, simply by changing the light engine. The integration of LEDGINE, brand new HID optics, electronic gear and controls is a response to the growing demand for energy savings. The new Iridium<sup>2</sup> HID optics are designed to deliver best-in-class lighting performance while offering tremendous flexibility in application. All these features, combined with Iridium<sup>2</sup>'s ease of installation and maintenance, ensure that customers enjoy low cost of ownership.

### Product data

General Information		Light source engine type	
Lamp family code	GRN78 [LED GreenLine 7800 lm]	Product family code	BGP352 [Iridium <sup>2</sup> LED Medium]
Light source replaceable	Yes	Lighting Technology	LED
Number of gear units	1 unit	Embedded control	-
Driver included	Yes	CE mark	Yes
Photocell	-	Warranty period	5 years
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Flammability mark	-
		ENEC mark	-
		EU RoHS compliant	No
Light Technical		Upward light output ratio	
		0	

## Iridium<sup>2</sup> LED Medium

Luminous Flux	7,021 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	94 lm/W
Color rendering index (CRI)	70
Number of light sources	48
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	150° x 62°
Optic type outdoor	Distribution medium

### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	46 A
Inrush time	0.25 ms
Power Consumption	60 W
Power Factor (Fraction)	0.9
Connection	Plug-in connector 3-pole Wieland/Adels compatible
Cable	-
Number of products on MCB of 16 A type B	11

### Temperature

Ambient temperature range	-25 to +25 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit regulating
Constant light output	No

### Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	Acrylate
Optic material	Polycarbonate
Optical cover material	Tempered glass
Fixation material	Stainless steel
Housing Color	Grey
Mounting device	Universal for diameter 48 to 76 mm
Optical cover shape	Flat

Optical cover finish	Clear
Overall length	751 mm
Overall width	358 mm
Overall height	183 mm
Effective projected area	0.08 m <sup>2</sup>
Dimensions (Height x Width x Depth)	183 x 358 x 751 mm
Parts color	All parts colored

### Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Phillips standard surge protection level
Protection class IEC	Safety class I

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.380, 0.380) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L80

### Application Conditions

Performance ambient temperature Tq	15 °C
------------------------------------	-------

### Product Data

Order product name	BGP352 GRN78-3S/740 DM AL GR T15
Full product name	BGP352 GRN78-3S/740 DM AL GR T15
Full product code	871829142467300
Order code	42467300
Material Nr. (12NC)	910925439548
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291424673
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291424673

## Iridium<sup>2</sup> LED Medium

### Dimensional drawing

