



# ClearWay

## BGP303 LED35-4S/740 PSR I DM50 D9 STD 42

ClearWay, LED module 3500 lm, 740 neutral white, Power supply unit regulating, Safety class I, Distribution medium, Philips standard surge protection level, Universal for diameter 42 to 60 mm

LED technology represents a breakthrough in lighting in many different respects. The light quality provided by LEDs, for example, has made our roads safer, while the tremendous efficacy of LEDs is helping cities reduce their energy bills. At Philips, we believe we can make even more roads safer, and help more municipalities achieve their goal of reducing energy consumption. That's why we have developed ClearWay – a LED road luminaire that is affordable yet does not compromise on light quality and energy efficiency.

### Product data

General Information		Light Technical	
Lamp family code	LED35 [LED module 3500 lm]	Flammability mark	For mounting on normally flammable surfaces
Light source replaceable	No	ENEC mark	ENEC mark
Number of gear units	1 unit	Glow-wire test	Temperature 960 °C, duration 5 s
Gear	EBD [Electronic regulating DALI]	EU RoHS compliant	No
Driver included	Yes		
Photocell	-		
Light source engine type	LED	Upward light output ratio	0
Product family code	BGP303 [ClearWay]	Luminous Flux	3,115 lm
Lighting Technology	LED	Standard tilt angle posttop	0°
Embedded control	-	Standard tilt angle side entry	0°
CE mark	Yes	Correlated Color Temperature (Nom)	4000 K
Warranty period	5 years	Luminous Efficacy (rated) (Nom)	135 lm/W
		Color rendering index (CRI)	>70

Number of light sources	1
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	150° x 62°
Optic type outdoor	Distribution medium

#### Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	46 A
Inrush time	0.25 ms
Power Consumption	23 W
Power Factor (Fraction)	0.89
Connection	Screw connection block 5-pole
Cable	-
Number of products on MCB of 16 A type B	11

#### Temperature

Ambient temperature range	-30 to +35 °C
---------------------------	---------------

#### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit regulating
Control interface	DALI
Constant light output	No

#### Mechanical and Housing

Housing Material	Aluminum
Reflector material	Polycarbonate
Optic material	Acrylate
Optical cover material	Tempered glass
Fixation material	Steel
Housing Color	Grey
Mounting device	Universal for diameter 42 to 60 mm
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	481 mm

Overall width	330 mm
Overall height	97 mm
Effective projected area	0.029 m <sup>2</sup>
Dimensions (Height x Width x Depth)	97 x 330 x 481 mm

#### Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Philips standard surge protection level
Protection class IEC	Safety class I

#### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.380, 0.380) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

#### Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.5 %
-------------------------------	-------

#### Application Conditions

Maximum dim level	0% (digital)
-------------------	--------------

#### Product Data

Order product name	BGP303 LED35-4S/740 PSR I DM50 D9 STD 42
Full product name	BGP303 LED35-4S/740 PSR I DM50 D9 STD 42
Full product code	871869637241800
Order code	37241800
Material Nr. (12NC)	910925452114
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696372418
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696372418

## Dimensional drawing



