



# UniStreet

## BGP204 LED120/740 I DM DDF2 48/60A

UniStreet Large, LED module 12000 lm, Distribution medium, DynaDimmer with fixed presets version 2, Universal for diameter 48 to 60 mm adjustable

At relatively low initial cost, the highly efficient LED-based UniStreet luminaire offers significant cost savings compared with conventional street lighting, ensuring full payback within a short period of time. Available in a choice of lumen packages, UniStreet allows point-to-point replacement of outdated conventional light sources and luminaires. The compact, slim luminaire is made of quality recyclable materials. And being a LED solution, it requires little maintenance. Core version design for high-volume projects at relatively low initial budget. Offer limited range of optics. Performer version design for customers who are preparing big renovation projects, TCO oriented

### Product data

General Information		Light source engine type	
Lamp family code	LED120 [LED module 12000 lm]	Light source engine type	LED
Light source replaceable	Yes	Product family code	BGP204 [UniStreet Large]
Number of gear units	1 unit	Lighting Technology	LED
Driver included	Yes	Glow-wire test	Temperature 650 °C, duration 5 s
Photocell	-	Flammability mark	-
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	CE mark	Yes
		ENEC mark	ENEC mark
		Warranty period	5 years
		EU RoHS compliant	No
		Embedded control	DynaDimmer with fixed presets version 2
		Light Technical	
		Upward light output ratio	0

Luminous Flux	11,050 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	100 lm/W
Color rendering index (CRI)	70
Number of light sources	6
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	154°
Optic type outdoor	Distribution medium

## Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	[DELETE] W
Average CLO power consumption	[DELETE] W
End CLO power consumption	[DELETE] W
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	106 W
Power Factor (Fraction)	0.98
Connection	Screw connection block 3-pole
Cable	-
Number of products on MCB of 16 A type B	8

## Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

## Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DynaDimmer
Control interface	Internal (no external connection)
Constant light output	No

## Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Tempered glass
Fixation material	Aluminum
Housing Color	Grey
Mounting device	Universal for diameter 48 to 60 mm adjustable

Optical cover shape	Flat
Optical cover finish	Clear
Overall length	755 mm
Overall width	355 mm
Overall height	98 mm
Effective projected area	0.04 m <sup>2</sup>
Dimensions (Height x Width x Depth)	98 x 355 x 755 mm

## Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Philips standard surge protection level
Protection class IEC	Safety class I

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.380, 0.380) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L92

## Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Programmable

## Product Data

Order product name	BGP204 LED120/740 I DM DDF2 48/60A
Full product name	BGP204 LED120/740 I DM DDF2 48/60A
Full product code	871869631873700
Order code	910925452261
Material Nr. (12NC)	910925452261
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696318737
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696318737

UniStreet

Dimensional drawing

