



EFix TPS262

TPS262 2x28W/830 HFD D6 PVCFR CCE SMT WH

EFix suspended mounted, 2, 28 W, 830 warm white, HF DALI, Semi-high-gloss optic double parabolic, Cable with CEE 7 plug 3-pole, White

The EFix TL5 luminaire range is a dedicated, affordable choice of innovative lighting that enables massive energy savings to be made when old electromagnetic installations are replaced by the latest Philips technology. The range's optical performance complies with the latest EN-12464 norms, ensuring improved lighting quality in every application. Used in combination with high-frequency gear, Philips MASTER TL5 lamps enable substantial energy savings to be made. These savings can be further increased by using a Luxsense daylight controller integrated into the luminaire. The practical design of EFix combines both surface-mounted (TCS260) and suspended (TPS262) luminaires in one design. Thanks to the luminaire's easily removable top cover, the beam can be adjusted to provide direct or direct/indirect lighting. EFix is supplied with lamps and is ready to install, minimizing installation time. EFix recessed TBS260 completes Philips' range of luminaires for general lighting applications in offices and shops.

Product data


General Information		Glow-wire test	
Lamp family code	TL5 [TL5]	Temperature 850 °C, duration 5 s	
Gear	HFD [HF DALI]		
Service tag	Yes		
Product family code	TPS262 [EFix suspended mounted]		
Embedded control	-		
CE mark	Yes		
Flammability mark	For mounting on normally flammable surfaces		
ENEC mark	ENEC mark		
		Light Technical	
		Number of light sources	2
		Light source color	830 warm white
		Optic type	Semi-high-gloss optic double parabolic
		Optical cover type	-

EFix TPS262

Operating and Electrical	
Input Voltage	220 to 240 V
Power Consumption	28 W
Cable	Cable with CEE 7 plug 3-pole
Mechanical and Housing	
Housing Color	White
Overall length	1,241 mm
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Protection class IEC	Safety class I
Application Conditions	
Suitable for random switching	Not applicable

Product Data	
Order product name	TPS262 2x28W/830 HFD D6 PVCFR CCE SMT WH
Full product name	TPS262 2x28W/830 HFD D6 PVCFR CCE SMT WH
Full product code	872790062346800
Order code	910925504812
Material Nr. (12NC)	910925504812
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900623468
Numerator - Packs per outer box	1
EAN/UPC - Case	8727900623468

Dimensional drawing



Product	B	C
TPS262 2x28W/830 HFD D6 PVCFR CCE SMT WH	500 mm	1,241 mm

