



CoreLine Trunking

LL120X LED90S/840 2x PSU VWB 5 WH

CoreLine Trunking - LED module, system flux 9000 lm - Power supply unit - Very wide beam

Whether for a new facility or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Trunking range of LED products can be used to replace general lighting. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Product data

General Information			
Number of light sources	6 pcs	Mounting	Suspension set 1-wire
Lamp family code	LED90S [LED module, system flux 9000 lm]	Ready-to-install	-
Beam angle of light source	120 °	Glow-wire test	Temperature 650 °C, duration 5 s
Light source color	840 neutral white	Flammability mark	For mounting on normally flammable surfaces
Light source replaceable	No	Accessories included	Mounting bracket for suspension wire
Number of gear units	2 units	CE mark	CE mark
Driver/power unit/transformer	Power supply unit	ENEC mark	ENEC mark
Driver included	Yes	Warranty period	3 years + 2 years upon registration
Optic type	Very wide beam	Mechanical accessories	-
Optical cover/lens type	-	Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore the median useful life (B50) value also represents the B10 value.
Luminaire light beam spread	130° x 88°	Constant light output	
Emergency lighting	-		
Internal wiring	Standard		
Feed-through wiring	Feed-through wiring 5-phase		
Connection	Connection unit 5-pole		
Cable	-		
Protection class IEC	Safety class I		


CoreLine Trunking

Number of products on MCB of 16 A type 12	
B	
RoHS mark	RoHS mark
Product family code	LL120X [CoreLine Trunking]
Unified glare rating CEN	Not applicable
Light Technical	
Light Distribution	Direct lighting
Operating and Electrical	
Input Voltage	220 to 240 V
Input Frequency	50 to 60 Hz
Control signal voltage	0-16 V DC DALI
Circuit	-
Circuit option	5 conductors
Inrush current	38 A
Inrush time	0.28 ms
Power Factor (Min)	0.95
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing Material	Steel
Reflector material	-
Optic material	Acrylate
Optical cover/lens material	Acrylate
Fixation material	Steel
Optical cover/lens finish	Clear
Overall length	3450 mm
Overall width	95 mm
Overall height	52 mm
Height	52 mm
Diameter	-
Color	White
Approval and Application	
Ingress protection code	IP20 [Finger-protected]


Mech. impact protection code	IK02 [0.2 J standard]
Initial Performance (IEC Compliant)	
Initial luminous flux (system flux)	9000 lm
Luminous flux tolerance	+/-7%
Initial LED luminaire efficacy	141 lm/W
Init. Corr. Color Temperature	4000 K
Init. Color Rendering Index	≥80
Initial chromaticity	(0.38, 0.38) SDCM <3
Initial input power	64 W
Power consumption tolerance	+/-11%
Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80
Application Conditions	
Ambient temperature range	-20 to +35 °C
Performance ambient temperature Tq	25 °C
Suitable for random switching	No
Product Data	
Full product code	871829190694000
Order product name	LL120X LED90S/840 2x PSU VWB 5 WH
EAN/UPC - Product	8718291906940
Order code	910925682968
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	910925682968
Net Weight (Piece)	6.910 kg

CoreLine Trunking

Dimensional drawing





CoreLine electr. units LL120X-LL122X



CoreLine electr. units LL120X-LL122X

CoreLine electr. units LL120X-LL122X

Photometric data



IFGU1_LL120X1xLED90S840VWB

IFPC1_LL120X1xLED90S840VWB

