



CoreLine Trunking

LL120X LED90S/840 2x PSU VWB 5 WH

CoreLine Trunking, LED module, system flux 9000 lm, Power supply unit (On/Off), Very wide beam

Whether for a new facility or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Trunking range of LED products can be used to replace general lighting. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Product data

| General Information | | | |
|--------------------------|--|------------------------------------|-------------------------------------|
| Lamp family code | LED90S [LED module, system flux 9000 lm] | CE mark | Yes |
| Light source replaceable | No | ENEC mark | ENEC mark |
| Number of gear units | 2 units | Warranty period | 3 years + 2 years upon registration |
| Driver included | Yes | EU RoHS compliant | Yes |
| Feed-through wiring | Feed-through wiring 5-phase | Light Technical | |
| Remarks | *-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value. | Luminous Flux | 9,000 lm |
| Service tag | Yes | Correlated Color Temperature (Nom) | 4000 K |
| Product family code | LL120X [CoreLine Trunking] | Luminous Efficacy (rated) (Nom) | 141 lm/W |
| Lighting Technology | LED | Color rendering index (CRI) | ≥80 |
| Glow-wire test | Temperature 650 °C, duration 5 s | Number of light sources | 6 |
| Flammability mark | For mounting on normally flammable surfaces | Beam angle of light source | 120 degree(s) |
| | | Light source color | 840 neutral white |
| | | Optic type | Very wide beam |
| | | Optical cover type | - |
| | | Luminaire light beam spread | 130° x 88° |
| | | Unified glare rating CEN | Not applicable |

CoreLine Trunking

| | |
|---|------------------------|
| Operating and Electrical | |
| Input Voltage | 220 to 240 V |
| Line Frequency | 50 to 60 Hz |
| Inrush current | 38 A |
| Inrush time | 0.28 ms |
| Power Consumption | 64 W |
| Power Factor (Fraction) | 0.95 |
| Connection | Connection unit 5-pole |
| Cable | - |
| Number of products on MCB of 16 A type 12 B | |

| | |
|---------------------------|---------------|
| Temperature | |
| Ambient temperature range | -20 to +35 °C |

| | |
|-------------------------------|----------------------------|
| Controls and Dimming | |
| Dimmable | No |
| Driver/power unit/transformer | Power supply unit (On/Off) |
| Constant light output | No |

| | |
|-------------------------------------|-------------------|
| Mechanical and Housing | |
| Housing Material | Steel |
| Reflector material | - |
| Optic material | Acrylate |
| Optical cover material | Acrylate |
| Fixation material | Steel |
| Housing Color | White |
| Optical cover finish | Clear |
| Overall length | 3,450 mm |
| Overall width | 95 mm |
| Overall height | 52 mm |
| Dimensions (Height x Width x Depth) | 52 x 95 x 3450 mm |

| | |
|------------------------------|-------------------------|
| Approval and Application | |
| Ingress protection code | IP20 [Finger-protected] |
| Mech. impact protection code | IK02 [0.2 J standard] |
| Protection class IEC | Safety class I |


| | |
|-------------------------------------|----------------------|
| Initial Performance (IEC Compliant) | |
| Luminous flux tolerance | +/-7% |
| Initial chromaticity | (0.38, 0.38) SDCM <3 |
| Power consumption tolerance | +/-11% |

| | |
|---|-----|
| Over Time Performance (IEC Compliant) | |
| Control gear failure rate at median useful life 50000 h | 5 % |
| Lumen maintenance at median useful life* 50000 h | L80 |


| | |
|------------------------------------|-------|
| Application Conditions | |
| Performance ambient temperature Tq | 25 °C |
| Suitable for random switching | No |

| | |
|---------------------------------|-----------------------------------|
| Product Data | |
| Order product name | LL120X LED90S/840 2x PSU VWB 5 WH |
| Full product name | LL120X LED90S/840 2x PSU VWB 5 WH |
| Full product code | 871829190694000 |
| Order code | 910925682968 |
| Material Nr. (12NC) | 910925682968 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8718291906940 |
| Numerator - Packs per outer box | 1 |
| EAN/UPC - Case | 8718291906940 |


Dimensional drawing




Dimensional drawing



| Product | A |
|-----------------------------------|----------|
| LL120X LED90S/840 2x PSU VWB 5 WH | 3,450 mm |



| Product | A |
|-----------------------------------|----------|
| LL120X LED90S/840 2x PSU VWB 5 WH | 3,464 mm |



| Product | A |
|-----------------------------------|----------|
| LL120X LED90S/840 2x PSU VWB 5 WH | 3,724 mm |

