



# Malaga SGS102

## SGS102 SON-T150W II MR-AS FG SKD 42/60

MALAGA, SON-T, 150 W, Safety class II, Moveable reflector with Allen screw, Flat glass, Universal for diameter 42 to 60 mm

Malaga is a versatile road-lighting luminaire. It offers modern styling and quality lighting for safe and comfortable driving, and for area illumination, with low investment and maintenance costs. The optical system has been designed to deliver good beam control and light output. Malaga provides optimal illuminance and good uniformity when the mounting height approximately equals the road width and the mast spacing is approximately 3.5 times the road width. It is suitable for post-top and side-entry mounting; a wall-mounting bracket is also available.

### Product data

| General Information            |                                     | Operating and Electrical     |   |
|--------------------------------|-------------------------------------|------------------------------|---|
| Lamp family code               | SON-T [SON-T]                       | Input Voltage                | 230 to 240 V  |
| Cap-Base                       | E40 [E40]                           | Power Consumption            | 150 W   |
| Gear                           | CONV [Conventional]                 | Mechanical and Housing       |   |
| Photocell                      | -                                   | Housing Color                | Grey  |
| Product family code            | SGS102 [MALAGA]                     | Mounting device              | Universal for diameter 42 to 60 mm  |
| CE mark                        | Yes                                 | Approval and Application     |   |
| ENEC mark                      | ENEC mark                           | Ingress protection code      | IP43/65 [Wire-protected, rain/spray-proof; dust penetration-protected, jet-proof] |
| Light Technical                |                                     | Mech. impact protection code | IK08 [5 J vandal-protected]   |
| Standard tilt angle posttop    | 15°                                 | Protection class IEC         | Safety class II   |
| Standard tilt angle side entry | 15°                                 | Product Data                 |   |
| Number of light sources        | 1                                   | Order product name           | SGS102 SON-T150W II MR-AS FG SKD 42/60  |
| Optical cover type             | Flat glass                          |                              |   |
| Optic type outdoor             | Moveable reflector with Allen screw |                              |   |

Malaga SGS102

|                               |  |
|-------------------------------|--|
| Full product name             | SGS102 SON-T150W II MR-AS FG SKD 42/60 |
| Full product code             | 872790063655000                        |
| Order code                    | 910925703412                           |
| Material Nr. (12NC)           | 910925703412                           |
| Numerator - Quantity Per Pack | 1                                      |

|                                 |               |
|---------------------------------|---------------|
| EAN/UPC - Product/Case          | 8727900636550 |
| Numerator - Packs per outer box | 1             |
| EAN/UPC - Case                  | 8727900636550 |

Dimensional drawing

