



# Selenium

## SGP340 SON-T400W K I FG SKD 76

Selenium LED, SON-T, 400 W, Safety class I, Flat glass, Spigot for diameter 76 mm

Selenium SGP340 is an efficient, ergonomic road-lighting luminaire. Its simple, rounded form reduces its daytime visual impact, allowing it to integrate into any kind of environment. Selenium incorporates the renowned T-POT reflector for excellent optical performance. Energy savings are possible by means of dimming with a switch or stand-alone Chronosense system (without pilot cable). Selenium is suitable for side-entry or post-top mounting, with a choice of three tilt angles for optimal installation (0, 5, 15°).


### Product data

| General Information            |                       | Optic type outdoor           |                                              |
|--------------------------------|-----------------------|------------------------------|----------------------------------------------|
| Lamp family code               | SON-T [SON-T]         | Open T-POT                   |                                              |
| Cap-Base                       | E40 [E40]             | Operating and Electrical     |                                              |
| Gear                           | CONV [Conventional]   | Input Voltage                | 230 to 240 V                                 |
| Photocell                      | -                     | Power Consumption            | 400 W                                        |
| Product family code            | BGP340 [Selenium LED] | Mechanical and Housing       |                                              |
| CE mark                        | Yes                   | Housing Color                | Gray                                         |
| ENEC mark                      | -                     | Mounting device              | Spigot for diameter 76 mm                    |
| Embedded control               | -                     | Overall height               | 232 mm                                       |
| Light Technical                |                       | Approval and Application     |                                              |
| Standard tilt angle posttop    | 5°                    | Ingress protection code      | IP66 [Dust penetration-protected, jet-proof] |
| Standard tilt angle side entry | 0°                    | Mech. impact protection code | IK08 [5 J vandal-protected]                  |
| Number of light sources        | 1                     | Protection class IEC         | Safety class I                               |
| Optical cover type             | Flat glass            |                              |                                              |

| Product Data        |                                |
|---------------------|--------------------------------|
| Order product name  | SGP340 SON-T400W K I FG SKD 76 |
| Full product name   | SGP340 SON-T400W K I FG SKD 76 |
| Full product code   | 872790063571300                |
| Order code          | 910925848612                   |
| Material Nr. (12NC) | 910925848612                   |

|                                 |               |
|---------------------------------|---------------|
| Numerator - Quantity Per Pack   | 1             |
| EAN/UPC - Product/Case          | 8727900635713 |
| Numerator - Packs per outer box | 1             |
| EAN/UPC - Case                  | 8727900635713 |

Dimensional drawing



| Product                        |
|--------------------------------|
| SGP340 SON-T400W K I FG SKD 76 |

