



GentleSpace gen2

BY471P GRN250S/840 PSD A50 G MBW SI SWP

GentleSpace 2, LED GreenLine system flux 25000 lm, 840 neutral white, Power supply unit with DALI interface, Asymmetrical mirror axis angle 50°, Glass, Silver

With the introduction of the GentleSpace LED luminaire in 2011, Philips achieved a breakthrough in high-bay lighting, offering a huge reduction in power consumption, a long service life and an innovative design. Now, with GentleSpace gen2, Philips continues to improve even further: an improved total cost of ownership, even in extreme conditions with the the GS-2 Xtreme version, which can be used up to +60 °C or 100,000 hrs of lifetime (L80), both ensured by an integrated over-heat protection. In addition, a wide variety of options – e.g. optics, coatings, mounting possibilities, cover materials and suitable for explosive zones 2/22 – are available to ensure an ideal solution for your application. Additionally, the GentleSpace gen2 can be equipped for use in a central emergency grid (PSED).

Product data

General Information		
Lamp family code	GRN250S [LED GreenLine system flux 25000 lm]	maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.
Cap-Base	- [-]	Service tag
Light source replaceable	Yes	Product family code
Number of gear units	2 units	BY471P [GentleSpace 2]
Gear	EB [Electronic]	Lighting Technology
Driver included	Yes	LED
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen	Glow-wire test
		Temperature 850 °C, duration 5 s
		Flammability mark
		For mounting on easily flammable surfaces
		CE mark
		Yes
		ENEC mark
		ENEC mark
		Warranty period
		5 years
		EU RoHS compliant
		Yes

GentleSpace gen2

Embedded control	-
------------------	---

Light Technical

Luminous Flux	25,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	152 lm/W
Color rendering index (CRI)	≥80
Number of light sources	16
Beam angle of light source	114 degree(s)
Light source color	840 neutral white
Optic type	Asymmetrical mirror axis angle 50°
Optical cover type	Glass
Luminaire light beam spread	56° x 33°
Unified glare rating CEN	Not applicable

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	9.6 A
Inrush time	2.3 ms
Power Consumption	164 W
Power Factor (Fraction)	0.9
Connection	External connector
Cable	Cord with plug Wieland/Adels compatible 5-pole

Number of products on MCB of 16 A type B 6

Temperature

Ambient temperature range	-30 to +45 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Acrylate
Optical cover material	Glass
Fixation material	Steel
Housing Color	Silver
Optical cover finish	Clear

Overall length	600 mm
Overall width	450 mm
Overall height	150 mm
Dimensions (Height x Width x Depth)	150 x 450 x 600 mm

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-11%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 50000 h	L85
Lumen maintenance at median useful life* 100000 h	L70

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	10%
Suitable for random switching	Yes

Product Data

Order product name	BY471P GRN250S/840 PSD A50 G MBW SI SWP
Full product name	BY471P GRN250S/840 PSD A50 G MBW SI SWP
Full product code	871869634596200
Order code	910925863183
Material Nr. (12NC)	910925863183
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696345962
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696345962

GentleSpace gen2

Dimensional drawing

