



# CoreLine Trunking

## LL120X 7X2.5 WH BC

CoreLine Trunking - 7 conductors cross-section 2.5 mm<sup>2</sup> - White  
- Blind cover

Whether for a new facility or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Trunking range of LED products can be used to replace general lighting. The process of selecting, installing and maintaining is so easy – it's a simple switch.

### Product data

General Information	
Connection	Connector with 2 additional wires for light regulation
Protection class IEC	Safety class I
CE mark	CE mark
Material	Steel
Mechanical accessories	Blind cover
Angle	-
Accessory color	White
Product family code	LL120X [ CoreLine Trunking]
Operating and Electrical	
Input Voltage	220 to 240 V
Input Frequency	50 to 60 Hz
Circuit option	7 conductors cross-section 2.5 mm <sup>2</sup>
Mechanical and Housing	
Overall length	3450 mm

Overall width	81 mm
Overall height	43 mm
Color	White
Dimensions (Height x Width x Depth)	43 x 81 x 3450 mm (1.7 x 3.2 x 135.8 in)
Approval and Application	
Ingress protection code	IP20 [ Finger-protected]
Mech. impact protection code	IK02 [ 0.2 J standard]
Application Conditions	
Ambient temperature range	-20 to +35 °C
Product Data	
Full product code	871869634648800
Order product name	LL120X 7X2.5 WH BC
EAN/UPC - Product	8718696346488
Order code	910925863236
Numerator - Quantity Per Pack	1

## CoreLine Trunking

---

<b>Numerator - Packs per outer box</b>	1
<b>Material Nr. (12NC)</b>	910925863236
<b>Net Weight (Piece)</b>	3.780 kg

---

