



# Iridium gen3 LED Medium

## BGP382 GRN105/740 I DM AL GR D9 SP

Iridium gen3 Medium, LED GreenLine 10500 lm, 740 neutral white, Safety class I, Distribution medium, Grey, Spigot

Iridium gen3 is the first truly intelligent luminaire designed for seamless connectivity. No hassle in commissioning – just install the luminaire and control it from a distance through CityTouch management software. Remote light management made easy! The new ‘plug & play’ concept has been designed to ensure safe and easy installation in just three steps: 1. Install the spigot, 2. Plug in the mains, 3. Tilt and close the luminaire. The luminaire’s high efficiency at system level ensures significant energy savings compared to existing conventional installations, offering a fast payback. Thanks to its wide choice of lumen packages, optics and color temperatures, Iridium gen3 fits most applications in residential areas. The luminaire’s neo-classical design guarantees a consistent look and feel for your surroundings.

### Product data

General Information			
Lamp family code	GRN105 [LED GreenLine 10500 lm]	maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire might automatically dim down to protect components	
Light source replaceable	Yes		
Number of gear units	1 unit		
Gear	EB [Electronic]		
Driver included	Yes		
Photocell	-	Light source engine type	LED
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen	Product family code	BGP382 [Iridium gen3 Medium]
		Lighting Technology	LED
		Embedded control	-
		CE mark	Yes

## Iridium gen3 LED Medium

Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 5 s
EU RoHS compliant	No

### Light Technical

Upward light output ratio	0
Luminous Flux	9,660 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	149 lm/W
Color rendering index (CRI)	70
Number of light sources	1
Light source color	740 neutral white
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	152°
Optic type outdoor	Distribution medium

### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	[delete] W
Average CLO power consumption	[delete] W
End CLO power consumption	[delete] W
Inrush current	45 A
Inrush time	0.285 ms
Power Consumption	65 W
Power Factor (Fraction)	0.98
Connection	Screw connection block 5-pole
Cable	-
Number of products on MCB of 16 A type B	10

### Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

### Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polycarbonate

Optical cover material	Polycarbonate
Fixation material	Aluminum
Housing Color	Grey
Mounting device	Spigot
Optical cover shape	Flat
Optical cover finish	Textured
Overall length	650 mm
Overall width	330 mm
Overall height	157 mm
Effective projected area	0.031 m²
Dimensions (Height x Width x Depth)	157 x 330 x 650 mm
Parts color	All parts colored

### Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Surge Protection (Common/Differential)	4/4 kV
Protection class IEC	Safety class I

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L80

### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	0% (digital)

### Product Data

Order product name	BGP382 GRN105/740 I DM AL GR D9 SP
Full product name	BGP382 GRN105/740 I DM AL GR D9 SP
Full product code	871869634721800
Order code	910925863310
Material Nr. (12NC)	910925863310
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696347218
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696347218

Iridium gen3 LED Medium

Dimensional drawing

