



GentleSpace gen2

BY472P GRN130S/840 PSD MB G SI

GentleSpace 2, LED GreenLine system flux 13000 lm, 840 neutral white, Power supply unit with DALI interface, Medium beam, Glass, Silver

With the introduction of the GentleSpace LED luminaire in 2011, Philips achieved a breakthrough in high-bay lighting, offering a huge reduction in power consumption, a long service life and an innovative design. Now, with GentleSpace gen2, Philips is setting a new standard in the market, with an improved total cost of ownership, even in extreme conditions. In addition, a high diversity of options are available to ensure an ideal solution for your application like optics, coatings and enabling the use of a central emergency grid (PSED).

Product data

| | | | |
|----------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------|--------------------------------------------------------|
| General Information | | | |
| Lamp family code | GRN130S [LED GreenLine system flux 13000 lm] | | useful life (B50) value also represents the B10 value. |
| Cap base | - [-] | Product family code | BY472P [GentleSpace 2] |
| Light source replaceable | Yes | Lighting Technology | LED |
| Number of gear units | Unit | Embedded control | - |
| Gear | EB [Electronic] | CE mark | Yes |
| Driver included | Yes | Warranty period | 5 years |
| Remarks | *- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median | Flammability mark | For mounting on easily flammable surfaces |
| | | ENEC mark | - |
| | | Glow-wire test | Temperature 650 °C, duration 5 s |
| | | EU RoHS compliant | Yes |
| | | Light Technical | |
| | | Luminous Flux | 13,000 lm |
| | | Correlated Colour Temperature | 4000 K |

GentleSpace gen2

| | |
|----------------------------------|-------------------|
| Luminous efficacy (rated) (nom.) | 149 lm/W |
| Colour rendering index (CRI) | ≥80 |
| Beam angle of light source | 114 degree(s) |
| Light source colour | 840 neutral white |
| Optic type | Medium beam |
| Optical cover type | Glass |
| Luminaire light beam spread | 40° x 40° |
| Unified Glare Rating (CEN) | 25 |

Operating and Electrical

| | |
|------------------------------------------|------------------------------------------------|
| Input Voltage | 220-240 V |
| Line Frequency | 50 to 60 Hz |
| Inrush current | 4.8 A |
| Inrush time | 2.3 ms |
| Power Consumption | 87 W |
| Power Factor (Fraction) | 0.9 |
| Connection | External connector |
| Cable | Cord with plug Wieland/Adels compatible 5-pole |
| Number of products on MCB of 16 A type B | 12 |

Temperature

| | |
|---------------------------|---------------|
| Ambient temperature range | -30 to +45 °C |
|---------------------------|---------------|

Controls and Dimming

| | |
|-------------------------------|---------------------------------------|
| Dimmable | Yes |
| Driver/power unit/transformer | Power supply unit with DALI interface |
| Control interface | DALI |
| Constant light output | No |

Mechanical and Housing

| | |
|-----------------------------|-----------------|
| Housing material | Aluminium |
| Reflector material | - |
| Optic material | Acrylate |
| Optical cover/lens material | Glass |
| Fixation material | Stainless steel |
| Housing Colour | Silver |
| Optical cover/lens finish | Clear |
| Overall length | 450 mm |
| Overall width | 350 mm |

| | |
|-------------------------------------|--------------------|
| Overall height | 130 mm |
| Dimensions (height x width x depth) | 130 x 350 x 450 mm |

Approval and Application

| | |
|------------------------------|----------------------------------------------|
| Ingress protection code | IP65 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code | IK07 [2 J reinforced] |
| Protection class IEC | Safety class I |

Initial Performance (IEC Compliant)

| | |
|-----------------------------|----------------------|
| Luminous flux tolerance | +/-7% |
| Initial chromaticity | (0.38, 0.38) SDCM <3 |
| Power consumption tolerance | +/-11% |

Over Time Performance (IEC Compliant)

| | |
|-----------------------------------------------------------|------|
| Control gear failure rate at median useful life 50,000 h | 5 % |
| Control gear failure rate at median useful life 100,000 h | 10 % |
| Lumen maintenance at median useful life* 50,000 h | L85 |
| Lumen maintenance at median useful life* 100,000 h | L70 |

Application Conditions

| | |
|------------------------------------|-------|
| Performance ambient temperature Tq | 25 °C |
| Maximum dim level | 10% |
| Suitable for random switching | No |

Product Data

| | |
|-----------------------------------|--------------------------------|
| Order product name | BY472P GRN130S/840 PSD MB G SI |
| Full product name | BY472P GRN130S/840 PSD MB G SI |
| Full EOC | 871869634844400 |
| Order code | 34844400 |
| Material no. (12 NC) | 910925863434 |
| SAP numerator – quantity per pack | 1 |
| EAN/UPC – Product/Case | 8718696348444 |
| Numerator – packs per outer box | 1 |
| EAN/UPC – Case | 8718696348444 |

GentleSpace gen2

Dimensional drawing

