



Pacific LED gen4

WT470C LED35S/840 PSU VWB L1600

PACIFIC LED WATERPROOF - 840 neutral white - Power supply unit - Very wide beam - Screw connection with pug and socket

PacificLED gen4 is a highly efficient and reliable LED waterproof luminaire that offers an excellent quality of light, with a uniform light distribution without visible striping or color artefacts. The range offers modular construction to enable ease of upgrade and maintenance. The new optical system provides distortion-free lighting with improved visual guidance, which makes it ideally suited to general industry, warehouses and parking areas. The range also offers the option of multiple optics to ensure an optimized lighting scheme for a wide range of applications. For industrial applications, PacificLED gen4 offers an open product architecture with toolless access to the gear tray and an innovative end-cap design with built-in connector for fast and easy installation. The single-piece mounting clamp ensures no small, loose components which could affect the primary production process.

Product data

General Information	
Beam angle of light source	120°
Light source colour	840 neutral white
Light source replaceable	Yes
Number of gear units	1 unit
Driver/power unit/transformer	PSU [Power supply unit]
Driver included	Yes
Optic type	VWB [Very wide beam]
Luminaire light beam spread	120° x 120°
Connection	Screw connection with pug and socket
Cable	-
Protection class IEC	Safety class I

Glow-wire test	Temperature 850 °C, duration 5 s
Flammability mark	D [For mounting on easily flammable surfaces]
CE mark	CE mark
ENEC mark	ENEC mark
Warranty period	5 years
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore the median useful life (B50) value also represents the B10 value.

Pacific LED gen4

Constant light output	No
Number of products on MCB	24
RoHS mark	RoHS mark
Product Family Code	WT470C [PACIFIC LED WATERPROOF]
Unified glare rating CEN	22

Operating and Electrical

Input voltage	220-240 V
Input frequency	50 to 60 Hz
Inrush current	17.8 A
Inrush time	0.282 ms
Power factor (min.)	0.96

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Housing material	Polycarbonate
Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Steel
Optical cover/lens finish	Clear
Overall length	1621 mm
Overall width	96 mm
Overall height	108 mm
Colour	White

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]

Initial Performance (IEC Compliant)

Initial luminous flux	3500 lm
Luminous flux tolerance	+/-7%

Initial LED luminaire efficacy	143 lm/W
Init. Corr. colour temperature	4000 K
Init. colour rendering index	>80
Initial chromaticity	(0.38, 0.38) SDCM <3
Initial input power	24.5 W
Power consumption tolerance	+/-11%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* L80 50000 h	
Lumen maintenance at median useful life* L70 100000 h	


Application Conditions

Ambient temperature range	-25 to +45 °C
Performance ambient temperature Tq	25 °C
Suitable for random switching	Not applicable

Product Data

Full product code	871869637931800
Order product name	WT470C LED35S/840 PSU VWB L1600
EAN/UPC – product	8718696379318
Order code	37931800
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	910925863809
Net weight (piece)	3.150 kg

Dimensional drawing



Pacific LED WT470C-WT482C

