



CoreLine Trunking

LL120X LED160S/840 2x PSD WB 7X2.5 VLC W

CoreLine Trunking, 6, LED module, system flux 16000 lm, Power supply unit with DALI interface, Wide beam, White

Whether for a new facility or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Trunking range of LED products can be used to replace general lighting. The process of selecting, installing and maintaining is so easy – it's a simple switch.


Product data

General Information		Flammability mark	
Lamp family code	LED160S [LED module, system flux 16000 lm]	For mounting on normally flammable surfaces	
Light source replaceable	No	ENEC mark	
Number of gear units	2 units	Glow-wire test	
Driver included	Yes	Temperature 650 °C, duration 5 s	
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	EU RoHS compliant	
Service tag	Yes	Yes	
Product family code	LL120X [CoreLine Trunking]	Light Technical	
Lighting Technology	LED	Luminous Flux	
CE mark	Yes	16,000 lm	
Warranty period	3 years + 2 years upon registration	Correlated Color Temperature (Nom)	
		4000 K	
		Luminous Efficacy (rated) (Nom)	
		148 lm/W	
		Color rendering index (CRI)	
		≥80	
		Number of light sources	
		6	
		Beam angle of light source	
		120 degree(s)	
		Light source color	
		840 neutral white	
		Optic type	
		Wide beam	
		Optical cover type	
		-	
		Luminaire light beam spread	
		100° x 94°	

CoreLine Trunking

Unified glare rating CEN	Not applicable
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	– W
Average CLO power consumption	– W
Inrush current	22 A
Inrush time	0.275 ms
Power Consumption	108 W
Power Factor (Fraction)	0.97
Connection	Connection unit 7-pole
Cable	–
Number of products on MCB of 16 A type B	24
Temperature	
Ambient temperature range	–20 to +35 °C
Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No
Mechanical and Housing	
Housing Material	Steel
Reflector material	–
Optic material	Acrylate
Optical cover material	Acrylate
Fixation material	Steel
Housing Color	White
Optical cover finish	Frosted
Overall length	3,450 mm
Overall width	95 mm
Overall height	52 mm
Dimensions (Height x Width x Depth)	52 x 95 x 3450 mm

Dimensional drawing



Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-2%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80
Application Conditions	
Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	No
Product Data	
Order product name	LL120X LED160S/840 2x PSD WB 7X2.5 VLC W
Full product name	LL120X LED160S/840 2x PSD WB 7X2.5 VLC W
Full product code	871869638086400
Order code	38086400
Material Nr. (12NC)	910925863965
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696380864
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696380864

