



CoreLine Trunking

LL120X LED150S/840 2x PSU O 5 WH

CoreLine Trunking, 6, LED module, system flux 15000 lm, Power supply unit (On/Off), Opal, Feed-through wiring 5-phase, White

Whether for a new facility or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Trunking range of LED products can be used to replace general lighting. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Product data

General Information		Flammability mark	
Lamp family code	LED150S [LED module, system flux 15000 lm]	For mounting on normally flammable surfaces	
Light source replaceable	No	ENEC mark	
Number of gear units	2 units	Glow-wire test	
Driver included	Yes	EU RoHS compliant	
Feed-through wiring	Feed-through wiring 5-phase	Light Technical	
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.	Luminous Flux	
Product family code	LL120X [CoreLine Trunking]	Correlated Colour Temperature	
Lighting Technology	LED	Luminous efficacy (rated) (nom.)	
CE mark	Yes	Colour rendering index (CRI)	
Warranty period	3 years + 2 years upon registration	Number of light sources	
		Beam angle of light source	
		Light source colour	
		Optic type	
		Optical cover type	
		Luminaire light beam spread	

CoreLine Trunking

Unified Glare Rating (CEN)	Not applicable
----------------------------	----------------

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
Inrush current	19 A
Inrush time	0.28 ms
Power Consumption	108 W
Power Factor (Fraction)	0.97
Connection	Connection unit 5-pole
Cable	-
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	-20 to +35 °C
---------------------------	---------------


Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing material	Steel
Reflector material	-
Optic material	Acrylate
Optical cover/lens material	Acrylate
Fixation material	Steel
Housing Colour	White
Optical cover/lens finish	Opal
Overall length	3,450 mm
Overall width	95 mm
Overall height	52 mm

Dimensional drawing



Dimensions (height x width x depth)	52 x 95 x 3450 mm
-------------------------------------	-------------------

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-2%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable
Suitable for random switching	No

Product Data

Order product name	LL120X LED150S/840 2x PSU O 5 WH
Full product name	LL120X LED150S/840 2x PSU O 5 WH
Full EOC	871869638100700
Order code	38100700
Material no. (12 NC)	910925863979
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696381007
Numerator – packs per outer box	1
EAN/UPC – Case	8718696381007

