



CoreLine Trunking

LL120X LED160S/840 2x PSD NB 7 VLC WH

CoreLine Trunking, 6, LED module, system flux 16000 lm, Power supply unit with DALI interface, Narrow beam, Feed-through wiring 7-phase, White

Whether for a new facility or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Trunking range of LED products can be used to replace general lighting. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Product data

General Information			
Lamp family code	LED160S [LED module, system flux 16000 lm]	CE mark	Yes
Light source replaceable	No	Warranty period	3 years + 2 years upon registration
Number of gear units	2 units	Flammability mark	For mounting on normally flammable surfaces
Driver included	Yes	ENEC mark	ENEC mark
Feed-through wiring	Feed-through wiring 7-phase	Glow-wire test	Temperature 650 °C, duration 5 s
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.	EU RoHS compliant	Yes
Product family code	LL120X [CoreLine Trunking]	Light Technical	
Lighting Technology	LED	Luminous Flux	16,000 lm
		Correlated Colour Temperature	4000 K
		Luminous efficacy (rated) (nom.)	148 lm/W
		Colour rendering index (CRI)	≥80
		Number of light sources	6
		Beam angle of light source	120 degree(s)
		Light source colour	840 neutral white
		Optic type	Narrow beam

CoreLine Trunking

Optical cover type	-
Luminaire light beam spread	48° x 66°
Unified Glare Rating (CEN)	Not applicable

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
Inrush current	22 A
Inrush time	0.275 ms
Power Consumption	108 W
Power Factor (Fraction)	0.97
Connection	Connection unit 7-pole
Cable	-
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	-20 to +35 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing material	Steel
Reflector material	-
Optic material	Acrylate
Optical cover/lens material	Acrylate
Fixation material	Steel
Housing Colour	White
Optical cover/lens finish	Clear
Overall length	3,450 mm
Overall width	95 mm

Overall height	52 mm
Dimensions (height x width x depth)	52 x 95 x 3450 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-2%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	No

Product Data

Order product name	LL120X LED160S/840 2x PSD NB 7 VLC WH
Full product name	LL120X LED160S/840 2x PSD NB 7 VLC WH
Full EOC	871869638113700
Order code	38113700
Material no. (12 NC)	910925863992
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696381137
Numerator – packs per outer box	1
EAN/UPC – Case	8718696381137

Dimensional drawing



