



CoreLine Trunking

LL121X LED80S/840 1x PSU WB 7 EL3 WH

CoreLine Trunking, 3, LED Module, system flux 8000 lm, Power supply unit (On/Off), Wide beam, Emergency lighting: three-hour duration, Feed-through wiring 5-phase, White

Whether for a new facility or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Trunking range of LED products can be used to replace general lighting. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Product data

General Information			
Lamp family code	LED80S [LED Module, system flux 8000 lm]	Warranty period	3 years + 2 years upon registration
Light source replaceable	No	Flammability mark	For mounting on normally flammable surfaces
Number of gear units	Unit	ENEC mark	ENEC mark
Driver included	Yes	Glow-wire test	Temperature 850 °C, duration 5 s
Feed-through wiring	Feed-through wiring 5-phase	EU RoHS compliant	Yes
Remarks	* - According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.		
Product family code	LL121X [CoreLine Trunking]	Light Technical	
Lighting Technology	LED	Luminous Flux	8,000 lm
CE mark	Yes	Correlated Colour Temperature	4000 K
		Luminous efficacy (rated) (nom.)	143 lm/W
		Colour rendering index (CRI)	≥80
		Number of light sources	3
		Beam angle of light source	120 degree(s)
		Light source colour	840 neutral white
		Optic type	Wide beam
		Optical cover type	-
		Luminaire light beam spread	100° x 94°

CoreLine Trunking

Unified Glare Rating (CEN)	Not applicable
----------------------------	----------------

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
Inrush current	19 A
Inrush time	0.28 ms
Power Consumption	56 W
Power Factor (Fraction)	0.97
Connection	Connector with 2 additional wires for addressable emergency lighting
Cable	-
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	-20 to +35 °C
---------------------------	---------------


Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing material	Steel
Reflector material	-
Optic material	Acrylate
Optical cover/lens material	Acrylate
Fixation material	Steel
Housing Colour	White
Optical cover/lens finish	Frosted
Overall length	1,730 mm
Overall width	95 mm

Dimensional drawing



Overall height	52 mm
Dimensions (height x width x depth)	52 x 95 x 1730 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-1%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable
Suitable for random switching	No

Product Data

Order product name	LL121X LED80S/840 1x PSU WB 7 EL3 WH
Full product name	LL121X LED80S/840 1x PSU WB 7 EL3 WH
Full EOC	871869638123600
Order code	38123600
Material no. (12 NC)	910925864003
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696381236
Numerator – packs per outer box	1
EAN/UPC – Case	8718696381236

