



# Maxos fusion

## LL523X LED100S/840 PSD DA25W 7 WH

Maxos fusion Panel, 840 neutral white, Power supply unit with DALI interface, Double asymmetric optic wide beam, White

Maxos fusion is an adaptable LED trunking system that offers an excellent quality of light while more than halving energy costs compared to fluorescent lamps. For retail applications, a family of linear panels, non-linear modules and a spot portfolio can be smoothly integrated into the track backbone to let your merchandise sparkle and stand out. For industrial applications, the focus is on reducing installation and maintenance cost by using fewer linear panels. With an electrical set-up of up to 13 wires, the freedom to position these fixtures as required and the integration of other services/third-party hardware, the system allows you to reduce ceiling clutter. It can also be easily re-configured to accommodate future layout changes. The infrastructure is enabled to integrate sensors for data collection, giving you the opportunity to use insightful granular information to support your business.

### Product data

General Information		Lighting Technology	
Light source replaceable	No	Value ladder	Specification
Number of gear units	Unit	CE mark	Yes
Driver included	Yes	Warranty period	5 years
Remarks	* - According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.	Flammability mark	For mounting on normally flammable surfaces
Product family code	LL523X [Maxos fusion Panel]	ENEC mark	ENEC mark
		Glow-wire test	Temperature 850 °C, duration 30 s
		EU RoHS compliant	Yes
		Light Technical	
		Luminous Flux	10,100 lm

# Maxos fusion

Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	142 lm/W
Colour rendering index (CRI)	>80
Flickering value (PstLM)	1
Stroboscopic effect	0.4
Beam angle of light source	120 degree(s)
Light source colour	840 neutral white
Optic type	Double asymmetric optic wide beam
Luminaire light beam spread	86° x 92°
Unified Glare Rating (CEN)	25

## Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	4.5 A
Inrush time	1 ms
Power Consumption	71 W
Power Factor (Fraction)	0.98
Connection	Connection unit 7-pole
Cable	-
Number of products on MCB of 16 A type B	18

## Temperature

Ambient temperature range	-20 to +35 °C
---------------------------	---------------

## Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

## Mechanical and Housing

Housing material	Steel
Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Steel
Housing Colour	White
Optical cover/lens finish	Textured
Overall length	2.276 mm
Overall width	62 mm

Overall height	14 mm
Dimensions (height x width x depth)	14 x 62 x 2276 mm

## Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Sustainability rating	Lighting for circularity
Protection class IEC	Safety class I

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.34, 0.35) SDCM <3
Power consumption tolerance	+/-11%

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 50,000 h	L95
Lumen maintenance at median useful life* 100,000 h	L85

## Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Not applicable

## Product Data

Order product name	LL523X LED100S/840 PSD DA25W 7 WH
Full product name	LL523X LED100S/840 PSD DA25W 7 WH
Full EOC	871869638451000
Order code	38451000
Material no. (12 NC)	910925864334
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696384510
Numerator – packs per outer box	1
EAN/UPC - Case	8718696384510

## Maxos fusion

### Dimensional drawing

