



UniStreet

BGS202 LED20/740 I DM 48/60A

UniStreet Mini, LED Module 2000 lm, 740 neutral white, Safety class I, Distribution medium, Side-entry for diameter 48 to 60 mm

At relatively low initial cost, the highly efficient LED-based UniStreet luminaire offers significant cost savings compared with conventional street lighting, ensuring full payback within a short period of time. Available in a choice of lumen packages, UniStreet allows point-to-point replacement of outdated conventional light sources and luminaires. The compact, slim luminaire is made of quality recyclable materials. And being a LED solution, it requires little maintenance. Core version design for high-volume projects at relatively low initial budget. Offer limited range of optics. Performer version design for customers who are preparing big renovation projects, TCO oriented

Product data

General Information		Light Technical	
Lamp family code	LED20 [LED Module 2000 lm]	Product family code	BGS202 [UniStreet Mini]
Light source replaceable	Yes	Lighting Technology	LED
Number of gear units	1 unit	Flammability mark	For mounting on normally flammable surfaces
Driver included	Yes	CE mark	Yes
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	ENEC mark	ENEC mark
Light source engine type	LED	Warranty period	5 years
		EU RoHS compliant	Yes
		Upward light output ratio	0
		Luminous Flux	1,812 lm
		Standard tilt angle posttop	0°

Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	113 lm/W
Color rendering index (CRI)	70
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	74° x 74°
Optic type outdoor	Distribution medium

Operating and Electrical

Input Voltage	230 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	[DELETE] W
Average CLO power consumption	[DELETE] W
End CLO power consumption	[DELETE] W
Inrush current	27 A
Inrush time	0.265 ms
Power Consumption	16 W
Power Factor (Fraction)	0.93
Connection	Connection unit 5-pole
Cable	-
Number of products on MCB of 16 A type B	18

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Aluminum
Housing Color	Gray
Mounting device	Side-entry for diameter 48 to 60 mm
Optical cover shape	Curved

Optical cover finish	Clear
Overall length	505 mm
Overall width	270 mm
Overall height	98 mm
Effective projected area	0.038 m²
Dimensions (Height x Width x Depth)	98 x 270 x 505 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Philips standard surge protection level
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L93

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable

Product Data

Order product name	BGS202 LED20/740 I DM 48/60A
Full product name	BGS202 LED20/740 I DM 48/60A
Full product code	871869698807700
Order code	910925864547
Material Nr. (12NC)	910925864547
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696988077
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696988077

Dimensional drawing

