



# UniStreet

## BGS202 LED25-4S/740 II DM11 76A

UniStreet Mini, LED Module 2500 lm, 740 neutral white, Safety class II, Distribution medium 11, Side-entry for diameter 76 mm

At relatively low initial cost, the highly efficient LED-based UniStreet luminaire offers significant cost savings compared with conventional street lighting, ensuring full payback within a short period of time. Available in a choice of lumen packages, UniStreet allows point-to-point replacement of outdated conventional light sources and luminaires. The compact, slim luminaire is made of quality recyclable materials. And being a LED solution, it requires little maintenance. Core version design for high-volume projects at relatively low initial budget. Offer limited range of optics. Performer version design for customers who are preparing big renovation projects, TCO oriented

### Product data

General Information		Flammability mark	
Lamp family code	LED25 [LED Module 2500 lm]	For mounting on normally flammable surfaces	
Light source replaceable	Yes	CE mark	Yes
Number of gear units	1 unit	ENEC mark	ENEC mark
Driver included	Yes	Warranty period	5 years
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	EU RoHS compliant	Yes
Light Technical			
Light source engine type	LED	Upward light output ratio	0
Product family code	BGS202 [UniStreet Mini]	Luminous Flux	2,225 lm
Lighting Technology	LED	Standard tilt angle posttop	0°
		Standard tilt angle side entry	0°
		Correlated Color Temperature (Nom)	4000 K
		Luminous Efficacy (rated) (Nom)	139 lm/W

Color rendering index (CRI)	70
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	80° x 80°
Optic type outdoor	Distribution medium 11

#### Operating and Electrical

Input Voltage	230 V
Line Frequency	50 to 60 Hz
Inrush current	22 A
Inrush time	0.29 ms
Power Consumption	16 W
Power Factor (Fraction)	0.94
Connection	Connection unit 5-pole
Cable	-
Number of products on MCB of 16 A type B	20

#### Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

#### Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

#### Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Aluminum
Housing Color	Grey
Mounting device	Side-entry for diameter 76 mm
Optical cover shape	Curved
Optical cover finish	Clear
Overall length	505 mm
Overall width	270 mm

Overall height	98 mm
Effective projected area	0.038 m²
Dimensions (Height x Width x Depth)	98 x 270 x 505 mm

#### Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Philips standard surge protection level
Protection class IEC	Safety class II

#### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

#### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L94

#### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable

#### Product Data

Order product name	BGS202 LED25-4S/740 II DM11 76A
Full product name	BGS202 LED25-4S/740 II DM11 76A
Full product code	871869698813800
Order code	910925864554
Material Nr. (12NC)	910925864554
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696988138
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696988138

## Dimensional drawing

