



# ClearWay gen2

## BGP307 LED45-4S/740 I DM50 48/60S

ClearWay gen2, LED Module 4500 lm, 740 neutral white, Safety class I, Distribution medium 50, Universal for diameter 48 to 60 mm adjustable

The ClearWay Gen2 enables you to enjoy the benefits of LED technology for urban lighting right from the start. This new second generation of the luminaire builds on the strengths of its predecessor and is designed to further minimise your Total Cost of Ownership. The ClearWay Gen2 significantly improves the most important aspects of the street-lighting experience compared to conventional urban lighting. Ideal for new streets and for renovating existing installations, this affordable range of urban ClearWay lighting solutions combines clean design, high-quality light with significant energy and maintenance savings. In short, ClearWay Gen2 means good-quality light with all the added benefits of LED – energy savings and long lifetime. Offering more benefits, yet packaged in a thinner and lighter design which makes it easier to install.

### Product data

| General Information      |   |   |                        |
|--------------------------|---|---|------------------------|
| Lamp family code         | LED45 [LED Module 4500 lm]  | value. * At extreme ambient temperatures the luminaire might automatically dim down to protect components |                        |
| Light source replaceable | Yes   |   |                        |
| Number of gear units     | Unit  |   |                        |
| Driver included          | Yes   | Light source engine type  | LED                    |
| Remarks                  | *- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 | Product family code   | BGP307 [ClearWay gen2] |
|                          |   | Lighting Technology   | LED                    |
|                          |   | Value ladder  | Performance            |
|                          |   | CE mark   | Yes                    |
|                          |   | Warranty period   | 5 years                |
|                          |   | Flammability mark   | -                      |
|                          |   | ENEC mark   | ENEC mark              |

## ClearWay gen2

|                   |    |
|-------------------|----|
| EU RoHS compliant | No |
|-------------------|----|

### Light Technical

|                                  |                        |
|----------------------------------|------------------------|
| Upwards light output ratio       | 0                      |
| Luminous Flux                    | 3,960 lm               |
| Standard tilt angle post-top     | 0°                     |
| Standard tilt angle side entry   | 0°                     |
| Correlated Colour Temperature    | 4000 K                 |
| Luminous efficacy (rated) (nom.) | 144 lm/W               |
| Colour rendering index (CRI)     | 70                     |
| Light source colour              | 740 neutral white      |
| Optic type                       | -                      |
| Optical cover type               | Flat glass             |
| Luminaire light beam spread      | 154° - 31° x 54°       |
| Optic type outdoor               | Distribution medium 50 |

### Operating and Electrical

|  |                          |
|--|--------------------------|
| Input Voltage                            | 220 to 240 V             |
| Line Frequency                           | 50 to 60 Hz              |
| Inrush current                           | 43 A                     |
| Inrush time                              | 0.26 ms                  |
| Power Consumption                        | 27.5 W                   |
| Power Factor (Fraction)                  | 0.95                     |
| Connection                               | Push-in connector 5-pole |
| Cable                                    | -                        |
| Number of products on MCB of 16 A type B | 20                       |

### Temperature

|                           |               |
|---------------------------|---------------|
| Ambient temperature range | -40 to +50 °C |
|---------------------------|---------------|

### Controls and Dimming

|                               |                            |
|-------------------------------|----------------------------|
| Dimmable                      | No                         |
| Driver/power unit/transformer | Power supply unit (On/Off) |
| Control interface             | -                          |
| Constant light output         | No                         |

### Mechanical and Housing

|                             |   |
|-----------------------------|---|
| Housing material            | Aluminium die cast                            |
| Reflector material          | -   |
| Optic material              | Polymethyl methacrylate                       |
| Optical cover/lens material | Tempered glass                                |
| Fixation material           | Aluminium                                     |
| Housing Colour              | Grey  |
| Mounting device             | Universal for diameter 48 to 60 mm adjustable |
| Optical cover/lens shape    | Flat  |
| Optical cover/lens finish   | Clear   |

|                                     |                   |
|-------------------------------------|-------------------|
| Overall length                      | 482 mm            |
| Overall width                       | 330 mm            |
| Overall height                      | 93 mm             |
| Effective projected area            | 0.1151 m²         |
| Dimensions (height x width x depth) | 93 x 330 x 482 mm |

### Approval and Application

|  |  |
|--|--|
| Ingress protection code                | IP66 [Dust penetration-protected, jet-proof]                                       |
| Mech. impact protection code           | IK09 [10 J]  |
| Surge Protection (Common/Differential) | Luminaire surge protection level up to 6 kV differential mode and 8 kV common mode |
| Sustainability rating                  | Lighting for circularity   |
| Protection class IEC                   | Safety class I   |
| Photobiological risk                   | Photobiological risk group 1 @ 200mm to EN62471                                    |
| Photobiological risk specification     | 3.1 m  |

### Initial Performance (IEC Compliant)

|                                       |                      |
|---------------------------------------|----------------------|
| Luminous flux tolerance               | +/-7%                |
| Initial chromaticity                  | (0.38, 0.38) SDCM <5 |
| Power consumption tolerance           | +/-10%               |
| Init. Color Rendering Index Tolerance | +/-2                 |

### Over Time Performance (IEC Compliant)

|   |       |
|---|-------|
| Driver failure rate at 5,000 hours                        | 0.5 % |
| Control gear failure rate at median useful life 50,000 h  | 5 %   |
| Control gear failure rate at median useful life 100,000 h | 10 %  |
| Lumen maintenance at median useful life* 100,000 h        | L97   |

### Application Conditions

|                                    |                |
|------------------------------------|----------------|
| Performance ambient temperature Tq | 25 °C          |
| Maximum dim level                  | Not applicable |

### Product Data

|                                   |                                   |
|-----------------------------------|-----------------------------------|
| Order product name                | BGP307 LED45-4S/740 I DM50 48/60S |
| Full product name                 | BGP307 LED45-4S/740 I DM50 48/60S |
| Full EOC                          | 871869698800800                   |
| Order code                        | 98800800                          |
| Material no. (12 NC)              | 910925864588                      |
| SAP numerator – quantity per pack | 1                                 |
| EAN/UPC – Product/Case            | 8718696988008                     |
| Numerator – packs per outer box   | 1                                 |
| EAN/UPC – Case                    | 8718696988008                     |

## ClearWay gen2

### Dimensional drawing

