



# CoreLine recessed

## RC134B LED27S/830 PSD W30L120 ELB3 NOC

CoreLine recessed, 34 W, 1200x300 mm, 2700 lm, 3000 K, DALI, ELB3h

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Recessed range of LED products can be used to replace functional luminaires in general lighting applications. The process of selecting, installing and maintaining is so easy – it's a simple switch. In addition, Coreline Recessed also provides the option of advanced connectivity and is ready to be connected to IoT based software applications such as Interact Pro.

### Warnings and Safety

- The product is IPX0 and as such is not protected against water ingress, so we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips/Signify cannot guarantee safe failure and product warranty will become void

### Product data

General Information			
Light source replaceable	No		useful life (B50) value also represents the B10 value.
Number of gear units	Unit	Product family code	RC134B [Coreline Recessed]
Driver included	Yes	Lighting Technology	LED
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median	Value ladder	Performance
		CE mark	Yes
		Warranty period	5 years
		Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	ENEC mark
		Glow-wire test	Temperature 850 °C, duration 30 s

## CoreLine recessed

EU RoHS compliant	Yes
-------------------	-----

### Light Technical

Luminous Flux	2,700 lm
Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	79 lm/W
Colour rendering index (CRI)	≥80
Light source colour	830 warm white
Optic type	Wide beam
Luminaire light beam spread	93°
Unified Glare Rating (CEN)	22

### Operating and Electrical

Input Voltage	220–240 V
Line Frequency	50 to 60 Hz
Inrush current	14.7 A
Inrush time	0.25 ms
Power Consumption	34 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	38

### Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

### Mechanical and Housing

Housing material	Steel
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	-
Housing Colour	White
Optical cover/lens finish	Textured

Overall length	1,197 mm
Overall width	297 mm
Overall height	41 mm
Dimensions (height x width x depth)	41 x 297 x 1197 mm

### Approval and Application

Ingress protection code	IP44 [Wire-protected, splash-proof]
Mech. impact protection code	IK02 [0.2 J standard]
Sustainability rating	-
Protection class IEC	Safety class I

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-8%
Initial chromaticity	(0.43, 0.40) SDCM <3
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L75

### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1% (no dimming in emergency mode)
Suitable for random switching	Yes

### Product Data

Order product name	RC134B LED27S/830 PSD W30L120 ELB3 NOC
Full product name	RC134B LED27S/830 PSD W30L120 ELB3 NOC
Full EOC	871869934841000
Order code	34841000
Material no. (12 NC)	910925864799
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699348410
Numerator – packs per outer box	1
EAN/UPC - Case	8718699348410

## CoreLine recessed

### Dimensional drawing

