



# CoreLine Surface-mounted

## SM134V LED37S/840 PSD W20L120 ELB3 OC

Coreline Surface - 840 neutral white - Power supply unit with DALI interface

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Surface-mounted range of LED products can be used to replace functional luminaires in general lighting applications. The process of selecting, installing and maintaining is so easy – it's a simple switch. ;InterAct Ready luminaires with integrated wireless communications in this family available, to be used with InterAct gateways, sensors and software.

### Product data

General Information		
Light source color	840 neutral white	
Light source replaceable	No	
Number of gear units	1 unit	
Driver/power unit/transformer	Power supply unit with DALI interface	
Driver included	Yes	
Optic type	Wide beam	
Luminaire light beam spread	81°	
Control interface	DALI	
Connection	Push-in connector and pull relief	
Cable	-	
Protection class IEC	Safety class I	
Glow-wire test	Temperature 850 °C, duration 30 s	
Flammability mark		For mounting on normally flammable surfaces
CE mark		CE mark
ENEC mark		ENEC mark
Warranty period		5 years
Remarks		*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore the median useful life (B50) value also represents the B10 value.
Constant light output		No


CoreLine Surface-mounted

Number of products on MCB of 16 A type 24	
B	
RoHS mark	RoHS mark
Product family code	SM134V [ Coreline Surface]
Unified glare rating CEN	19
Operating and Electrical	
Input Voltage	220 to 240 V
Input Frequency	50 to 60 Hz
Inrush current	22 A
Inrush time	0.275 ms
Power Factor (Min)	0.9
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Housing Material	Steel
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Steel
Optical cover/lens finish	Textured
Overall length	1170 mm
Overall width	197 mm
Overall height	47 mm
Color	White
Approval and Application	
Ingress protection code	IP20 [ Finger-protected]
Mech. impact protection code	IK02 [ 0.2 J standard]
Initial Performance (IEC Compliant)	
Initial luminous flux (system flux)	3700 lm

Luminous flux tolerance	+/-8%
Initial LED luminaire efficacy	106 lm/W
Init. Corr. Color Temperature	4000 K
Init. Color Rendering Index	≥80
Initial chromaticity	(0.38, 0.38) SDCM <3
Initial input power	35 W
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L75
Application Conditions	
Ambient temperature range	+10 to +40 °C
Performance ambient temperature Tq	25 °C
Maximum dim level	1% (no dimming in emergency mode)
Suitable for random switching	Yes
Product Data	
Full product code	871869934890800
Order product name	SM134V LED375/840 PSD W20L120 ELB3 OC
EAN/UPC - Product	8718699348908
Order code	910925864849
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	910925864849
Net Weight (Piece)	4.000 kg



Dimensional drawing



CoreLine Surface-mounted SM134V

## CoreLine Surface-mounted

