



# ClearWay

## BGP303 LED35-4S/740 PSU II DM11 C450CE 4

ClearWay, LED module 3500 lm, 740 neutral white, Power supply unit (On/Off), Safety class II, Distribution medium 11, Philips standard surge protection level, Cable 0.45 m with connector 2-pole, Universal for diameter 42 to 60 mm

LED technology represents a breakthrough in lighting in many different respects. The light quality provided by LEDs, for example, has made our roads safer, while the tremendous efficacy of LEDs is helping cities reduce their energy bills. At Philips, we believe we can make even more roads safer, and help more municipalities achieve their goal of reducing energy consumption. That's why we have developed ClearWay – a LED road luminaire that is affordable yet does not compromise on light quality and energy efficiency.

### Product data

General Information		EU RoHS compliant	
Lamp family code	LED35 [LED module 3500 lm]	No	
Light source replaceable	No		
Number of gear units	1 unit		
Driver included	Yes		
Light source engine type	LED		
Product family code	BGP303 [ClearWay]		
Lighting Technology	LED		
Flammability mark	For mounting on normally flammable surfaces		
CE mark	Yes		
ENEC mark	ENEC mark		
Warranty period	5 years		
Light Technical			
Upward light output ratio	0		
Luminous Flux	3,115 lm		
Standard tilt angle posttop	0°		
Standard tilt angle side entry	0°		
Correlated Color Temperature (Nom)	4000 K		
Luminous Efficacy (rated) (Nom)	135 lm/W		
Color rendering index (CRI)	>70		
Light source color	740 neutral white		
Optical cover type	Flat glass		
Luminaire light beam spread	150° x 62°		

Optic type outdoor	Distribution medium 11
<b>Operating and Electrical</b>	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
End CLO power consumption	- W
Inrush current	46 A
Inrush time	0.250 ms
Power Consumption	22.6 W
Power Factor (Fraction)	0.90
Connection	Screw connection block 5-pole
Cable	Cable 0.45 m with connector 2-pole
Number of products on MCB of 16 A type B 11	

#### Temperature

Ambient temperature range	-30 to +35 °C
---------------------------	---------------


#### Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

#### Mechanical and Housing

Housing Material	Aluminum
Reflector material	Polycarbonate
Optic material	Acrylate
Optical cover material	Tempered glass
Fixation material	Steel
Housing Color	Gray
Mounting device	Universal for diameter 42 to 60 mm
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	481 mm
Overall width	330 mm

### Dimensional drawing



Overall height	97 mm
Effective projected area	0.029 m²
Dimensions (Height x Width x Depth)	97 x 330 x 481 mm

#### Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Philips standard surge protection level
Protection class IEC	Safety class II

#### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.380, 0.380) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

#### Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.5 %
-------------------------------	-------

#### Application Conditions

Maximum dim level	Not applicable
-------------------	----------------

#### Product Data

Order product name	BGP303 LED35-4S/740 PSU II DM11 C450CE 4
Full product name	BGP303 LED35-4S/740 PSU II DM11 C450CE 4
Full product code	871869934899100
Order code	910925864858
Material Nr. (12NC)	910925864858
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699348991
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699348991

