



ClearWay

BGP303 LED69-4S/740 PSU I DM11 76

ClearWay, LED module 6900 lm, 740 neutral white, Power supply unit (On/Off), Safety class I, Distribution medium 11, Philips standard surge protection level, Spigot for diameter 76 mm

LED technology represents a breakthrough in lighting in many different respects. The light quality provided by LEDs, for example, has made our roads safer, while the tremendous efficacy of LEDs is helping cities reduce their energy bills. At Philips, we believe we can make even more roads safer, and help more municipalities achieve their goal of reducing energy consumption. That's why we have developed ClearWay – a LED road luminaire that is affordable yet does not compromise on light quality and energy efficiency.

Product data

General Information		EU RoHS compliant	
Lamp family code	LED69 [LED module 6900 lm]	No	
Light source replaceable	No		
Number of gear units	1 unit		
Driver included	Yes		
Light source engine type	LED		
Product family code	BGP303 [ClearWay]		
Lighting Technology	LED		
Flammability mark	For mounting on normally flammable surfaces		
CE mark	Yes		
ENEC mark	ENEC mark		
Warranty period	5 years		
		Light Technical	
		Upward light output ratio	0
		Luminous Flux	6,160 lm
		Standard tilt angle posttop	0°
		Standard tilt angle side entry	0°
		Correlated Color Temperature (Nom)	4000 K
		Luminous Efficacy (rated) (Nom)	138 lm/W
		Color rendering index (CRI)	>70
		Light source color	740 neutral white
		Optical cover type	Flat glass
		Luminaire light beam spread	150° x 62°

Optic type outdoor	Distribution medium 11
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
End CLO power consumption	- W
Inrush current	46 A
Inrush time	0.250 ms
Power Consumption	45.5 W
Power Factor (Fraction)	0.96
Connection	Screw connection block 5-pole
Cable	-
Number of products on MCB of 16 A type B 11	

Temperature

Ambient temperature range	-30 to +35 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	Polycarbonate
Optic material	Acrylate
Optical cover material	Tempered glass
Fixation material	Steel
Housing Color	Grey
Mounting device	Spigot for diameter 76 mm
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	536 mm

Overall width	330 mm
Overall height	98 mm
Effective projected area	0.029 m ²
Dimensions (Height x Width x Depth)	98 x 330 x 536 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Philips standard surge protection level
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.380, 0.380) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.5 %
-------------------------------	-------

Application Conditions

Maximum dim level	Not applicable
-------------------	----------------

Product Data

Order product name	BGP303 LED69-4S/740 PSU I DM11 76
Full product name	BGP303 LED69-4S/740 PSU I DM11 76
Full product code	871869934914100
Order code	910925864873
Material Nr. (12NC)	910925864873
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699349141
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699349141

Dimensional drawing

