



# UniStreet

## BGP243 LED100/740 I DM D9 48/60A

UniStreet Medium, LED module 10000 lm, 740 neutral white, Safety class I, Distribution medium, Flat glass, Side-entry for diameter 48 to 60 mm

At relatively low initial cost, the highly efficient LED-based UniStreet luminaire offers significant cost savings compared with conventional street lighting, ensuring full payback within a short period of time. Available in a choice of lumen packages, UniStreet allows point-to-point replacement of outdated conventional light sources and luminaires. The compact, slim luminaire is made of quality recyclable materials. And being a LED solution, it requires little maintenance. Core version design for high-volume projects at relatively low initial budget. Offer limited range of optics. Performer version design for customers who are preparing big renovation projects, TCO oriented

### Product data

General Information		Product family code	
Lamp family code	LED100 [LED module 10000 lm]	Product family code	BGP243 [UniStreet Medium]
Light source replaceable	Yes	Lighting Technology	LED
Number of gear units	1 unit	Flammability mark	For mounting on normally flammable surfaces
Driver included	Yes	CE mark	Yes
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	ENEC mark	ENEC mark
Light source engine type	LED	Warranty period	5 years
		EU RoHS compliant	Yes
		Light Technical	
		Upward light output ratio	0
		Luminous Flux	9,400 lm
		Standard tilt angle posttop	0°

Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	119 lm/W
Color rendering index (CRI)	70
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	74° x 74°
Optic type outdoor	Distribution medium

#### Operating and Electrical

Input Voltage	230 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	[Delete] W
Average CLO power consumption	[Delete] W
End CLO power consumption	[Delete] W
Inrush current	53 A
Inrush time	0.300 ms
Power Consumption	79 W
Power Factor (Fraction)	0.90
Connection	Connection unit 5-pole
Cable	-
Number of products on MCB of 16 A type B	8

#### Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

#### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

#### Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Aluminum
Housing Color	Gray
Mounting device	Side-entry for diameter 48 to 60 mm
Optical cover shape	Curved

Optical cover finish	Clear
Overall length	580 mm
Overall width	353 mm
Overall height	98 mm
Effective projected area	0.42 m²
Dimensions (Height x Width x Depth)	98 x 353 x 580 mm

#### Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Philips standard surge protection level
Protection class IEC	Safety class I

#### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

#### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* L96	100000 h

#### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	0% (digital)

#### Product Data

Order product name	BGP243 LED100/740 I DM D9 48/60A
Full product name	BGP243 LED100/740 I DM D9 48/60A
Full product code	871869698865700
Order code	910925864892
Material Nr. (12NC)	910925864892
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696988657
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696988657

Dimensional drawing

