



CoreLine surface-mounted

SM134V LED37S/830 W60L60 IA1 NOC

CoreLine surface-mounted, 35.4 W, 600x600 mm, 3700 lm, 3000 K, Wireless, Interact Ready

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Surface-mounted range of LED products can be used to replace functional luminaires in general lighting applications. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that The environment in which The luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void

Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Service tag	Yes
Product family code	SM134V [Coreline Surface]
Connectivity	Interact Ready
Lighting Technology	LED
Value ladder	Performance
Embedded control	Interact SNS210 sensor

CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 850 °C, duration 30 s
EU RoHS compliant	Yes

Light Technical	
Luminous Flux	3,700 lm

CoreLine surface-mounted

Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	104.5 lm/W
Color rendering index (CRI)	≥80
Light source color	830 warm white
Optic type	Wide beam
Luminaire light beam spread	93°
Unified glare rating CEN	22

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	22 A
Inrush time	0.275 ms
Power Consumption	35.4 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Wireless Dim
Driver/power unit/transformer	Power supply unit regulating external
Control interface	Wireless
Constant light output	No

Mechanical and Housing

Housing Material	Steel
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	White
Optical cover finish	Textured
Overall length	597 mm
Overall width	597 mm

Overall height	47 mm
Dimensions (Height x Width x Depth)	47 x 597 x 597 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Sustainability rating	-
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-8%
Initial chromaticity	(0.43, 0.40) SDCM <3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	1 %
Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L75


Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

Product Data

Order product name	SM134V LED37S/830 W60L60 IA1 NOC
Full product name	SM134V LED37S/830 W60L60 IA1 NOC
Full product code	871869699668300
Order code	99668300
Material Nr. (12NC)	910925865189
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696996683
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696996683

Dimensional drawing



CoreLine surface-mounted

