



# ClearWay gen2

## BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18

ClearWay gen2, LED Module 2500 lm, 740 neutral white, Safety class II, Distribution medium 11, Universal for diameter 48 to 60 mm adjustable

The ClearWay Gen2 enables you to enjoy the benefits of LED technology for urban lighting right from the start. This new second generation of the luminaire builds on the strengths of its predecessor and is designed to further minimise your Total Cost of Ownership. The ClearWay Gen2 significantly improves the most important aspects of the street-lighting experience compared to conventional urban lighting. Ideal for new streets and for renovating existing installations, this affordable range of urban ClearWay lighting solutions combines clean design, high-quality light with significant energy and maintenance savings. In short, ClearWay Gen2 means good-quality light with all the added benefits of LED – energy savings and long lifetime. Offering more benefits, yet packaged in a thinner and lighter design which makes it easier to install.

### Product data

General Information			
Lamp family code	LED25 [LED Module 2500 lm]	value. * At extreme ambient temperatures the luminaire might automatically dim down to protect components	
Light source replaceable	Yes		
Number of gear units	Unit		
Driver included	Yes	Light source engine type	LED
Remarks	* - According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10	Product family code	BGP307 [ClearWay gen2]
		Lighting Technology	LED
		CE mark	Yes
		Warranty period	5 years
		Flammability mark	-
		ENEC mark	ENEC mark
		EU RoHS compliant	No

## ClearWay gen2

<b>Light Technical</b>	
Upwards light output ratio	0
Luminous Flux	2,088 lm
Standard tilt angle post-top	0°
Standard tilt angle side entry	0°
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	134 lm/W
Colour rendering index (CRI)	70
Light source colour	740 neutral white
Optic type	-
Optical cover type	Flat glass
Luminaire light beam spread	160° - 42° x 54°
Optic type outdoor	Distribution medium 11
<b>Operating and Electrical</b>	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	15.6 W
Average CLO power consumption	16 W
End CLO power consumption	16.2 W
Inrush current	12 A
Inrush time	0.27 ms
Power Consumption	15.6 W
Power Factor (Fraction)	0.99
Connection	Push-in connector 5-pole
Cable	-
Number of products on MCB of 16 A type B	48
<b>Temperature</b>	
Ambient temperature range	-40 to +50 °C
<b>Controls and Dimming</b>	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DynaDimmer
Control interface	-
Constant light output	Yes
<b>Mechanical and Housing</b>	
Housing material	Aluminium die cast
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover/lens material	Tempered glass
Fixation material	Aluminium
Housing Colour	Grey
Mounting device	Universal for diameter 48 to 60 mm adjustable
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Overall length	482 mm

Overall width	330 mm
Overall height	93 mm
Effective projected area	0.1151 m²
Dimensions (height x width x depth)	93 x 330 x 482 mm
<b>Approval and Application</b>	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Surge Protection (Common/Differential)	Luminaire surge protection level up to 6 kV differential mode and 8 kV common mode
Sustainability rating	Lighting for circularity
Protection class IEC	Safety class II
Photobiological risk	Photobiological risk group 1 @ 200mm to EN62471
Photobiological risk specification	3.1 m
<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2
<b>Over Time Performance (IEC Compliant)</b>	
Driver failure rate at 5,000 hours	0.5 %
Control gear failure rate at median useful life 50,000 h	5 %
Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 100,000 h	L100
<b>Application Conditions</b>	
Performance ambient temperature Tq	25 °C
Maximum dim level	0% (digital)
<b>Product Data</b>	
Order product name	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18
Full product name	BGP307 LED25-4S/740 II DM11 CLO-DDF1 D18
Full EOC	871869699709300
Order code	99709300
Material no. (12 NC)	910925865231
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696997093
Numerator – packs per outer box	1
EAN/UPC – Case	8718696997093

ClearWay gen2

Dimensional drawing

