



ClearWay gen2

BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18

ClearWay gen2, LED module 3500 lm, 740 neutral white, Safety class II, Distribution medium 11, Universal for diameter 48 to 60 mm adjustable

ClearWay Gen2 enables you to enjoy the benefits of LED technology for urban lighting right from the start. This new second generation of the luminaire builds on the strengths of its predecessor and is designed to further minimize your Total Cost of Ownership. ClearWay Gen2 significantly improves the most important aspects of the street lighting experience compared to conventional urban lighting. Ideal for new streets and for renovating existing installations, this affordable range of urban ClearWay lighting solutions combines clean design, high-quality light with significant energy and maintenance savings. In short, ClearWay Gen2 means good quality light with all the added benefits of LED – energy savings and long lifetime. Offering more benefits, yet packaged in a thinner and lighter design, which makes it easier to install.

Product data

General Information		
Lamp family code	LED35 [LED module 3500 lm]	
Light source replaceable	Yes	
Number of gear units	1 unit	
Driver included	Yes	
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire might automatically dim down to protect components	
Light source engine type		LED
Product family code		BGP307 [ClearWay gen2]
Lighting Technology		LED
CE mark		Yes
Warranty period		5 years
Flammability mark		-
ENEC mark		ENEC mark

ClearWay gen2

EU RoHS compliant	No
Light Technical	
Upward light output ratio	0
Luminous Flux	2,958 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	141 lm/W
Color rendering index (CRI)	70
Light source color	740 neutral white
Optic type	-
Optical cover type	Flat glass
Luminaire light beam spread	160° - 42° x 54°
Optic type outdoor	Distribution medium 11
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	21 W
Average CLO power consumption	21 W
End CLO power consumption	21.5 W
Inrush current	43 A
Inrush time	0.26 ms
Power Consumption	21 W
Power Factor (Fraction)	0.93
Connection	Push-in connector 5-pole
Cable	Cable 10 m without plug
Number of products on MCB of 16 A type B	10
Temperature	
Ambient temperature range	-40 to +50 °C
Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DynaDimmer
Control interface	-
Constant light output	Yes
Mechanical and Housing	
Housing Material	Aluminum die cast
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover material	Tempered glass
Fixation material	Aluminum
Housing Color	Gray
Mounting device	Universal for diameter 48 to 60 mm adjustable
Optical cover shape	Flat

Optical cover finish	Clear
Overall length	482 mm
Overall width	330 mm
Overall height	93 mm
Effective projected area	0.1151 m²
Dimensions (Height x Width x Depth)	93 x 330 x 482 mm
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
Sustainability rating	Lighting for circularity
Protection class IEC	Safety class II
Photobiological risk	Photobiological risk group 1 @ 200mm to EN62471
Photobiological risk specification	3.1 m
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2
Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50000 h	5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L100
Application Conditions	
Performance ambient temperature Tq	25 °C
Maximum dim level	0% (digital)
Product Data	
Order product name	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18
Full product name	BGP307 LED35-4S/740 II DM11 CLO-DDF2 D18
Full product code	871869699878600
Order code	910925865402
Material Nr. (12NC)	910925865402
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696998786
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696998786

ClearWay gen2

Dimensional drawing

