



# UniStreet

## BGP202 LED40/740 I DM D9 48/60A

UniStreet Mini - LED module 4000 lm - 740 neutral white - Safety class I - Distribution medium - Side-entry for diameter 48-60 mm

At relatively low initial cost, the highly efficient LED-based UniStreet luminaire offers significant cost savings compared with conventional street lighting, ensuring full payback within a short period of time. Available in a choice of lumen packages, UniStreet allows point-to-point replacement of outdated conventional light sources and luminaires. The compact, slim luminaire is made of quality recyclable materials. And being a LED solution, it requires little maintenance.

### Product data

General Information		Light Technical	
Lamp family code	LED40 [ LED module 4000 lm]	ENEC mark	ENEC mark
Light source colour	740 neutral white	Warranty period	5 years
Light source replaceable	Yes	Outdoor optic type	Distribution medium
Number of gear units	1 unit	Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components
Driver/power unit/transformer	PSD [ Power supply unit with DALI interface]	Constant light output	No
Driver included	Yes	Number of products on MCB	20
Optical cover/lens type	FG [ Flat glass]	RoHS mark	RoHS mark
Luminaire light beam spread	74° x 74°	LED engine type	LED
Control interface	DALI	Product Family Code	BGP202 [ UniStreet Mini]
Connection	Connection unit 5-pole		
Cable	-		
Protection class IEC	Safety class I	Upward light output ratio	0
Flammability mark	F [ For mounting on normally flammable surfaces]	Standard tilt angle post-top	0°
CE mark	CE mark		

Standard tilt angle side entry	0°
--------------------------------	----

**Operating and Electrical**

Input voltage	230 V
Input frequency	50 to 60 Hz
Initial CLO power consumption	[DELETE] W
Average CLO power consumption	[DELETE] W
End CLO power consumption	[DELETE] W
Inrush current	22 A
Inrush time	0.290 ms
Power factor (min.)	0.94

**Controls and Dimming**

Dimmable	Yes
----------	-----

**Mechanical and Housing**

Housing material	Aluminium die-cast
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Aluminum
Mounting device	48/60S [ Side-entry for diameter 48-60 mm]
Optical cover/lens shape	Curved
Optical cover/lens finish	Clear
Overall length	505 mm
Overall width	270 mm
Overall height	98 mm
Overall diameter	0 mm
Effective projected area	0.038 m <sup>2</sup>
Colour	Grey

**Approval and Application**

Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [ 5 J vandal-protected]
Surge protection (common/differential)	Philips standard surge protection level kV

**Initial Performance (IEC Compliant)**

Initial luminous flux	3555 lm
Luminous flux tolerance	+/-7%
Initial LED luminaire efficacy	115 lm/W
Init. Corr. colour temperature	4000 K
Init. colour rendering index	70
Initial chromaticity	(0.38, 0.38) SDCM <5
Initial input power	31 W
Power consumption tolerance	+/-11%

**Application Conditions**


Ambient temperature range	-40 to +50 °C
Maximum dimming level	0% (digital)

**Product Data**

Full product code	871869698819000
Order product name	BGP202 LED40/740 I DM D9 48/60A
EAN/UPC – product	8718696988190
Order code	98819000
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	910925866088
Net weight (piece)	4.110 kg



**Dimensional drawing**



UniStreet BGP/BGS202/203/204

