



UniStreet

BGP202 LED20/740 II DM D9 48/60A

UniStreet Mini, LED Module 2000 lm, 740 neutral white, Safety class II, Distribution medium, Side-entry for diameter 48 to 60 mm

At relatively low initial cost, the highly efficient LED-based UniStreet luminaire offers significant cost savings compared with conventional street lighting, ensuring full payback within a short period of time. Available in a choice of lumen packages, UniStreet allows point-to-point replacement of outdated conventional light sources and luminaires. The compact, slim luminaire is made of quality recyclable materials. And being a LED solution, it requires little maintenance.

Product data

General Information		EU RoHS compliant	
Lamp family code	LED20 [LED Module 2000 lm]	Yes	
Light source replaceable	Yes		
Number of gear units	Unit		
Driver included	Yes		
Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components		
Light source engine type	LED		
Product family code	BGP202 [UniStreet Mini]		
Lighting Technology	LED		
CE mark	Yes		
Warranty period	5 years		
Flammability mark	For mounting on normally flammable surfaces		
ENEC mark	ENEC mark		
Light Technical			
Upwards light output ratio	0		
Luminous Flux	1,812 lm		
Standard tilt angle post-top	0°		
Standard tilt angle side entry	0°		
Correlated Colour Temperature	4000 K		
Luminous efficacy (rated) (nom.)	113 lm/W		
Colour rendering index (CRI)	70		
Light source colour	740 neutral white		
Optical cover type	Flat glass		
Luminaire light beam spread	74° x 74°		
Optic type outdoor	Distribution medium		

Operating and Electrical

Input Voltage	230 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	[DELETE] W
Average CLO power consumption	[DELETE] W
End CLO power consumption	[DELETE] W
Inrush current	22 A
Inrush time	0.290 ms
Power Consumption	16 W
Power Factor (Fraction)	0.93
Connection	Connection unit 5-pole
Cable	-
Number of products on MCB of 16 A type B	20

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing material	Aluminium die cast
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Aluminium
Housing Colour	Grey
Mounting device	Side-entry for diameter 48 to 60 mm
Optical cover/lens shape	Curved
Optical cover/lens finish	Clear
Overall length	505 mm
Overall width	270 mm

Overall height	98 mm
Overall diameter	0 mm
Effective projected area	0.038 m²
Dimensions (height x width x depth)	98 x 270 x 505 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Philips standard surge-protection level
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Driver failure rate at 5,000 hours	0.50 %
------------------------------------	--------

Application Conditions

Maximum dim level	0% (digital)
-------------------	--------------

Product Data

Order product name	BGP202 LED20/740 II DM D9 48/60A
Full product name	BGP202 LED20/740 II DM D9 48/60A
Full EOC	871869698824400
Order code	98824400
Material no. (12 NC)	910925866126
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696988244
Numerator – packs per outer box	1
EAN/UPC - Case	8718696988244

Dimensional drawing



