



# LumiStreet

## BGP212 LED56-4S/740 II DM50 D9 48/60A

LumiStreet Mini, LED module 5600 lm, 740 neutral white, Safety class II, Distribution medium 50, Side-entry for diameter 48 to 60 mm

Many local authorities today have an outdated public lighting installation that urgently needs to be replaced, yet have only a limited budget available. We have the answer to their needs. With its compact design and modern LED architecture, LumiStreet is a versatile, cost-effective luminaire that fulfils basic functional road lighting requirements. It is made of high-quality components that ensure long lifetime and low maintenance cost. The result? A road lighting luminaire that provides effective illumination while at the same time cutting energy and maintenance bills. Core version design for high-volume projects at relatively low initial budget. Offer limited range of optics. Performer version design for customer who are preparing big renovation projects, TCO oriented.

### Product data

General Information		Light Technical	
Lamp family code	LED56 [LED module 5600 lm]	Flammability mark	For mounting on normally flammable surfaces
Light source replaceable	Yes	CE mark	Yes
Number of gear units	1 unit	ENEC mark	ENEC mark
Driver included	Yes	Warranty period	5 years
Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components	EU RoHS compliant	Yes
Light source engine type	LED	Upward light output ratio	0
Product family code	BGP212 [LumiStreet Mini]	Luminous Flux	4,816 lm
Lighting Technology	LED	Standard tilt angle posttop	0°
		Standard tilt angle side entry	0°

Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	134 lm/W
Color rendering index (CRI)	70
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	154° - 31° x 54°
Optic type outdoor	Distribution medium 50

#### Operating and Electrical

Input Voltage	230 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	0 W
Average CLO power consumption	[DELETE] W
End CLO power consumption	[DELETE] W
Inrush current	22 A
Inrush time	0.29 ms
Power Consumption	36 W
Power Factor (Fraction)	0.98
Connection	Connection unit 5-pole
Cable	-
Number of products on MCB of 16 A type B 20	

#### Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

#### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

#### Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Aluminum
Housing Color	Grey
Mounting device	Side-entry for diameter 48 to 60 mm

Optical cover shape	Curved
Optical cover finish	Clear
Overall length	505 mm
Overall width	270 mm
Overall height	98 mm
Overall diameter	0 mm
Effective projected area	0.038 m²
Dimensions (Height x Width x Depth)	98 x 270 x 505 mm

#### Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Philips standard surge protection level
Protection class IEC	Safety class II

#### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

#### Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.50 %
-------------------------------	--------

#### Application Conditions

Maximum dim level	0% (digital)
-------------------	--------------

#### Product Data

Order product name	BGP212 LED56-4S/740 II DM50 D9 48/60A
Full product name	BGP212 LED56-4S/740 II DM50 D9 48/60A
Full product code	871869934775800
Order code	910925866205
Material Nr. (12NC)	910925866205
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699347758
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699347758

Dimensional drawing

