



DigiStreet

BGP761 LED50-/830 II DM11 DGR D9 62

DigiStreet Mini - LED module 5000 lm - 830 warm white - Safety class II (II) - Distribution medium 11 - Dark gray - Dimming via external communication DALI - Spigot for diameter 62 mm

Developed with the aim of becoming your long-term partner, the system-ready architecture of DigiStreet enables you to enjoy the benefits of connected lighting systems today and also gets the city ready for the innovations to come! Its two sockets enable you to connect directly to the Philips CityTouch system and it is also prepared to connect you to the future innovations of IoT. Next to this, each individual luminaire is uniquely identifiable, thanks to the Philips Service tag application. With a simple scan of a QR code, placed on the inside of the mast door, you gain instant access to the luminaire configuration, making maintenance and programming operations faster and easier, no matter what stage of the luminaire's lifetime. DigiStreet is also equipped with dedicated light recipes that: 1) maintain optimal ecosystems for bats or 2) preserve a dark night sky.

Product data

General Information		Connection	SI [Screw connection block]
Lamp family code	LED50 [LED module 5000 lm]	Cable	-
Light source colour	830 warm white	Protection class IEC	Safety class II (II)
Light source replaceable	No	Flammability mark	NO [-]
Number of gear units	1 unit	CE mark	CE mark
Driver/power unit/transformer	PSU [Power supply unit]	ENEC mark	ENEC mark
Driver included	Yes	Warranty period	5 years
Optical cover/lens type	FG [Flat glass]	Outdoor optic type	Distribution medium 11
Luminaire light beam spread	160° - 42° x 54°	Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components
Control interface	DALI	Constant light output	No
Light regulation	Dimming via external communication DALI		

Number of products on MCB	11
RoHS mark	RoHS mark
LED engine type	LED
Product Family Code	BGP761 [DigiStreet Mini]

Light Technical

Upward light output ratio	0
Standard tilt angle post-top	0°
Standard tilt angle side entry	0°

Operating and Electrical

Input voltage	220-240 V
Input frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
End CLO power consumption	- W
Inrush current	46 A
Inrush time	0.25 ms
Power factor (min.)	0.96

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Housing material	Aluminum
Reflector material	Polycarbonate
Optic material	Acrylate
Optical cover/lens material	Glass
Fixation material	Steel
Mounting device	62 [Spigot for diameter 62 mm]
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Overall length	860 mm
Overall width	236 mm

Overall height	107 mm
Effective projected area	0.0666 m ²
Colour	Dark gray

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]

Initial Performance (IEC Compliant)


Initial luminous flux	4550 lm
Luminous flux tolerance	+/-7%
Initial LED luminaire efficacy	120 lm/W
Init. Corr. colour temperature	3000 K
Init. colour rendering index	80
Initial chromaticity	(0.43, 0.40) SDCM <5
Initial input power	38 W
Power consumption tolerance	+/-11%

Application Conditions


Ambient temperature range	-40 to +50 °C
Maximum dimming level	Not applicable

Product Data

Full product code	871869637694200
Order product name	BGP761 LED50-/830 II DM11 DGR D9 62
EAN/UPC – product	8718696376942
Order code	37694200
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	910925866238
Net weight (piece)	7.610 kg



Dimensional drawing



DigiStreet BGP760-BTP764

