



3-circuit Square RCS750

RCS750 3C L1000 BK (XTS4100-2)

3-circuit Square RCS750, Normal, Black, Tool-protected

The Philips 3-circuit square track system consists of an anodised aluminium profile in natural anodised or painted white in lengths of 1, 2, 3 and 4 m. It contains four electrical conductors allowing easy creation of any required configuration: horizontal or vertical, recessed or surface-mounted, on the wall, on free-standing panels or floating. All luminaires have their separate power supply and can be switched selectively by phase or by circuit. Because the luminaires are easy to move, by simply clicking them in place in the adaptor on the track, changes in the lighting and presentation can be made very simply. All 230V projectors in the Philips range can be installed on this track system. All the associated accessories are common to both the surface-mounted and recessed models and guarantee a good electrical and mechanical connection.

Product data

| General Information | |
|--------------------------|----------------------------------|
| Accessory color | Black |
| Glow-wire test | Temperature 850 °C, duration 5 s |
| Mechanical and Housing | |
| Overall length | 1,000 mm |
| Approval and Application | |
| Ingress protection code | IP30 [Tool-protected] |
| Protection class IEC | Safety class I |

| Product Data | |
|---------------------------------|--------------------------------|
| Order product name | RCS750 3C L1000 BK (XTS4100-2) |
| Full product name | RCS750 3C L1000 BK (XTS4100-2) |
| Full product code | 871155979851600 |
| Order code | 79851600 |
| Material Nr. (12NC) | 910930013218 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711559798516 |
| Numerator - Packs per outer box | 1 |
| EAN/UPC - Case | 8711559798516 |

3-circuit Square RCS750

Dimensional drawing

