



# Mini 300 LED gen2

## BBP400 ECO75-3S/757 I PRW WH MDU MWS PH

Mini300 LED gen2, LED EconomyLine 7500 lm, Petrol rotational symmetric wide, Movement detection unit, Photocell included

The Mini 300 LED gen2 luminaires provides highly efficient, controlable and manageable lighting solutions for petrols station canopies and low bay applications. These ultra-efficient retrofit LED fixtures are the latest development of the Philips Mini 300 range offering outstanding light quality, effective thermal management, and long lifespan. Reduced maintenance, replacement and energy costs also mean a short payback period, making Mini 300 LED gen2 a shining example of how businesses can save money without compromising on light quality by opting for energy efficient LED products. The integrated movement detector, daylight sensor and scheduler options enables further energy savings. Our Mini 300 LED gen2 app gives users control in ways that are simply not possible with other luminaires – reading status, managing and controlling lighting from ground level using a laptop or Smartphone via Bluetooth - removing the need for access cranes or ladders.

### Product data

General Information	
Lamp family code	ECO75 [LED EconomyLine 7500 lm]
Light source replaceable	Yes
Number of gear units	Unit
Driver included	Yes
Photocell	Photocell included
Light source engine type	LED
Product family code	BBP400 [Mini300 LED gen2]
Lighting Technology	LED
Embedded control	Movement detection unit
CE mark	Yes

Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
Glow-wire test	Temperature 960 °C, duration 5 s
EU RoHS compliant	No
Light Technical	
Upwards light output ratio	0
Luminous Flux	7,900 lm
Standard tilt angle post-top	0°
Standard tilt angle side entry	0°

## Mini 300 LED gen2

Correlated Colour Temperature	5700 K
Luminous efficacy (rated) (nom.)	123 lm/W
Colour rendering index (CRI)	≥70
Light source colour	757 cool white
Optical cover type	Flat glass
Luminaire light beam spread	135°
Optic type outdoor	Petrol rotational symmetric wide

### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	46 A
Inrush time	0.25 ms
Power Consumption	54 W
Power Factor (Fraction)	0.97
Connection	Screw connection block 5-pole
Cable	Cable 2.0 m with screw connector

Number of products on MCB of 16 A type B 11

### Temperature

Ambient temperature range	-30 to +40 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit regulating external
Control interface	-
Constant light output	No

### Mechanical and Housing

Housing material	Aluminium
Reflector material	-
Optic material	Acrylate
Optical cover/lens material	Glass
Fixation material	Steel
Housing Colour	White
Mounting device	-
Optical cover/lens shape	Convex lens
Optical cover/lens finish	Clear

Overall length	413 mm
Overall width	413 mm
Overall height	95 mm
Effective projected area	0 m <sup>2</sup>
Dimensions (height x width x depth)	95 x 413 x 413 mm

### Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Philips standard surge-protection level
Protection class IEC	Safety class I

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.341, 0.329) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

### Over Time Performance (IEC Compliant)

Driver failure rate at 5,000 hours	0.1 %
------------------------------------	-------


### Application Conditions

Maximum dim level	10%
-------------------	-----

### Product Data

Order product name	BBP400 ECO75-3S/757 I PRW WH MDU MWS PH
Full product name	BBP400 ECO75-3S/757 I PRW WH MDU MWS PH
Full EOC	871829189052200
Order code	89052200
Material no. (12 NC)	910930205371
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718291890522
Numerator – packs per outer box	1
EAN/UPC - Case	8718291890522

## Dimensional drawing



## Mini 300 LED gen2

