



# GentleSpace GreenWarehouse

## BY470X GRN130S/840 NB GC ACW SI

GentleSpace GreenWarehouse, LED GreenLine system flux 13000 lm, 840 neutral white, Narrow beam, Clear glass, ActiLume wireless, Silver

This dedicated system makes it easy for warehouse developers and facility managers to achieve maximum energy savings. It seamlessly integrates state-of-the-art LED lighting with an easy-to-use and reliable networked control solution. When the situation on the work floor changes, settings such as dimming levels and timing can be changed wirelessly by the end-users themselves. Luminaires can be combined in groups across the layout, and re-zoning them does not require a hardware change, thus minimizing commissioning costs. The system delivers savings over and above the actual efficiency of the LEDs and is future-proof. Easy to understand, easy to design-in, and easy to use, the GreenWarehouse is simplicity itself.

### Product data

General Information		
Lamp family code	GRN130S [LED GreenLine system flux 13000 lm]	maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.
Light source replaceable	Yes	Product family code
Number of gear units	1 unit	BY470X [GentleSpace GreenWarehouse]
Driver included	Yes	Lighting Technology
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen	Glow-wire test
		Temperature 650 °C, duration 5 s
		Flammability mark
		For mounting on easily flammable surfaces
		CE mark
		Yes
		ENEC mark
		ENEC mark
		Warranty period
		5 years

# GentleSpace GreenWarehouse

EU RoHS compliant	Yes
Embedded control	ActiLume wireless

## Light Technical

Luminous Flux	13,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	148 lm/W
Color rendering index (CRI)	≥80
Number of light sources	8
Beam angle of light source	114 degree(s)
Light source color	840 neutral white
Optic type	Narrow beam
Optical cover type	Clear glass
Luminaire light beam spread	30° x 25°
Unified glare rating CEN	19

## Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	4.8 A
Inrush time	2.3 ms
Power Consumption	88 W
Power Factor (Fraction)	0.9
Connection	External connector
Cable	Cable 0.5 m with cable connector 3-pole
Number of products on MCB of 16 A type B	12

## Temperature

Ambient temperature range	-20 to +45 °C
---------------------------	---------------

## Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	-
Constant light output	No

## Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Acrylate
Optical cover material	Glass
Fixation material	Stainless steel
Housing Color	Silver

Optical cover finish	Clear
Overall length	502 mm
Overall width	350 mm
Overall height	211 mm
Dimensions (Height x Width x Depth)	211 x 350 x 502 mm

## Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-11%

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 50000 h	L85
Lumen maintenance at median useful life* 100000 h	L70

## Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	10%
Suitable for random switching	Yes

## Product Data

Order product name	BY470X GRN130S/840 NB GC ACW SI
Full product name	BY470X GRN130S/840 NB GC ACW SI
Full product code	871869632132400
Order code	910930205890
Material Nr. (12NC)	910930205890
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696321324
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696321324

# GentleSpace GreenWarehouse

## Dimensional drawing

