



GentleSpace GreenWarehouse

BY470X GRN130S/840 HRO GC ACW SI

GentleSpace GreenWarehouse - LED GreenLine system flux 13000 lm - 840 neutral white - High-rack optic - Clear glass - ActiLume wireless - Silver

This dedicated system makes it easy for warehouse developers and facility managers to achieve maximum energy savings. It seamlessly integrates state-of-the-art LED lighting with an easy-to-use and reliable networked control solution. When the situation on the work floor changes, settings such as dimming levels and timing can be changed wirelessly by the end-users themselves. Luminaires can be combined in groups across the layout, and re-zoning them does not require a hardware change, thus minimizing commissioning costs. The system delivers savings over and above the actual efficiency of the LEDs and is future-proof. Easy to understand, easy to design-in, and easy to use, the GreenWarehouse is simplicity itself.

Product data

General Information			
Number of light sources	8 [8 pcs]	Optic type	HRO [High-rack optic]
Lamp family code	GRN130S [LED GreenLine system flux 13000 lm]	Optical cover/lens type	GC [Clear glass]
Beam angle of light source	114 °	Luminaire light beam spread	16° x 47°
Light source colour	840 neutral white	Embedded control	ACW [ActiLume wireless]
Light source replaceable	Yes	Control interface	-
Number of gear units	1 unit	Connection	CE [External connector]
Driver/power unit/transformer	PSD [Power supply unit with DALI interface]	Cable	Cord 0.5 m with cable connector 3-pole
Driver included	Yes	Protection class IEC	Safety class I (I)
		Mounting	SMT [Suspension set twin, triangle]
		Glow-wire test	650/5 [Temperature 650 °C, duration 5 s]

GentleSpace GreenWarehouse

Flammability mark	D [For mounting on easily flammable surfaces]
CE mark	CE mark
ENEC mark	ENEC mark
Design award-winner mark	Design Award Winner 2014
Warranty period	5 years
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.
Constant light output	No
Number of products on MCB (16 A type B)	12
EU RoHS compliant	Yes
Product family code	BY470X [GentleSpace GreenWarehouse]
Unified glare rating CEN	Not applicable

Operating and Electrical

Input Voltage	220 to 240 V
Input frequency	50 to 60 Hz
Control signal voltage	0-16 V DC DALI
Inrush current	4.8 A
Inrush time	2.3 ms
Power factor (min.)	0.9

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Housing material	Aluminum
Reflector material	-
Optic material	Acrylate
Optical cover/lens material	Glass
Fixation material	Stainless steel
Optical cover/lens finish	Clear
Overall length	502 mm
Overall width	350 mm
Overall height	211 mm
Colour	Silver
Dimensions (height x width x depth)	211 x 350 x 502 mm (8.3 x 13.8 x 19.8 in)

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]

Initial Performance (IEC Compliant)

Initial luminous flux	13000 lm
Luminous flux tolerance	+/-7%
Initial LED luminaire efficacy	148 lm/W
Init. Corr. Colour Temperature	4000 K
Init. Colour rendering index	≥80
Initial chromaticity	(0.38, 0.38) SDCM <3
Initial input power	88 W
Power consumption tolerance	+/-11%

Over Time Performance (IEC Compliant)


Control gear failure rate at median useful life 50,000 h	5 %
Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 50,000 h	L85
Lumen maintenance at median useful life* 100,000 h	L70

Application Conditions

Ambient temperature range	-20 to +45 °C
Performance ambient temperature Tq	25 °C
Maximum dimming level	10%
Suitable for random switching	Yes

Product Data

Full product code	871869632135500
Order product name	BY470X GRN130S/840 HRO GC ACW SI
EAN/UPC – product	8718696321355
Order code	32135500
SAP numerator – quantity per pack	1
Numerator – packs per outer box	1
SAP material	910930205893
Net Weight (Piece)	9.800 kg



GentleSpace GreenWarehouse

Dimensional drawing



GentleSpace Warehouse system BY470X/BY471X

