



GentleSpace GreenWarehouse

BY470X GRN130S/840 HRO PC ACW SI

GentleSpace GreenWarehouse, LED GreenLine system flux 13000 lm, 840 neutral white, High-rack optic, Polycarbonate bowl/cover, ActiLume wireless, Silver

This dedicated system makes it easy for warehouse developers and facility managers to achieve maximum energy savings. It seamlessly integrates state-of-the-art LED lighting with an easy-to-use and reliable networked control solution. When the situation on the work floor changes, settings such as dimming levels and timing can be changed wirelessly by the end-users themselves. Luminaires can be combined in groups across the layout, and re-zoning them does not require a hardware change, thus minimizing commissioning costs. The system delivers savings over and above the actual efficiency of the LEDs and is future-proof. Easy to understand, easy to design-in, and easy to use, the GreenWarehouse is simplicity itself.

Product data

General Information			
Lamp family code	GRN130S [LED GreenLine system flux 13000 lm]		maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.
Light source replaceable	Yes	Product family code	BY470X [GentleSpace GreenWarehouse]
Number of gear units	1 unit	Lighting Technology	LED
Driver included	Yes	Glow-wire test	Temperature 650 °C, duration 5 s
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen	Flammability mark	For mounting on easily flammable surfaces
		CE mark	Yes
		ENEC mark	ENEC mark
		Warranty period	5 years

GentleSpace GreenWarehouse

EU RoHS compliant	Yes
Embedded control	ActiLume wireless

Light Technical

Luminous Flux	13,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	148 lm/W
Color rendering index (CRI)	≥80
Number of light sources	8
Beam angle of light source	114 degree(s)
Light source color	840 neutral white
Optic type	High-rack optic
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	16° x 47°
Unified glare rating CEN	Not applicable

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	4.8 A
Inrush time	2.3 ms
Power Consumption	88 W
Power Factor (Fraction)	0.9
Connection	External connector
Cable	Cable 0.5 m with cable connector 3-pole
Number of products on MCB of 16 A type B	12

Temperature

Ambient temperature range	-20 to +45 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Acrylate
Optical cover material	Polycarbonate
Fixation material	Stainless steel
Housing Color	Silver

Optical cover finish	Clear
Overall length	502 mm
Overall width	350 mm
Overall height	211 mm
Dimensions (Height x Width x Depth)	211 x 350 x 502 mm

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-11%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 50000 h	L85
Lumen maintenance at median useful life* 100000 h	L70

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	10%
Suitable for random switching	Yes

Product Data

Order product name	BY470X GRN130S/840 HRO PC ACW SI
Full product name	BY470X GRN130S/840 HRO PC ACW SI
Full product code	871869632147800
Order code	910930205906
Material Nr. (12NC)	910930205906
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696321478
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696321478

Dimensional drawing

