PHILIPS Lighting



GentleSpace Green Warehouse system

BY471X GRN250S/840 HRO PC ACW SI

GentleSpace GreenWarehouse, LED GreenLine system flux 25000 lm, 840 neutral white, High-rack optic, Polycarbonate bowl/cover, ActiLume wireless, Silver

This dedicated system makes it easy for warehouse developers and facility managers to achieve maximum energy savings. It seamlessly integrates state-ofthe-art LED lighting with an easy-to-use and reliable networked control solution. When the situation on the work floor changes, settings such as dimming levels and timing can be changed wirelessly by the end-users themselves. Luminaires can be combined in groups across the layout, and re-zoning them does not require a hardware change, thus minimizing commissioning costs. The system delivers savings over and above the actual efficiency of the LEDs and is future-proof. Easy to understand, easy to design-in, and easy to use, the GreenWarehouse is simplicity itself.

Product data

General Information	
Lamp family code	GRN250S [LED GreenLine system flux 25000
	lm]
Light source replaceable	Yes
Number of gear units	2 units
Driver included	Yes
Remarks	*- According to the Lighting Europe guidance
	paper 'Evaluating performance of LED based
	luminaires – January 2018': statistically there
	is no relevant difference in lumen

	maintenance between the B50 and, for
	example, the B10. Therefore, the median
	useful life (B50) value also represents the
	B10 value.
Product family code	BY471X [GentleSpace GreenWarehouse]
Lighting Technology	LED
Embedded control	ActiLume wireless
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on easily flammable surfaces

GentleSpace Green Warehouse system

ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 5 s
EU RoHS compliant	Yes
Light Technical	
Luminous Flux	25,000 lm

Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	152 lm/W
Colour rendering index (CRI)	≥80
Beam angle of light source	114 degree(s)
Light source colour	840 neutral white
Optic type	High-rack optic
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	16° x 47°
Unified Glare Rating (CEN)	Not applicable

Optical cover/lens finish	Clear
Overall length	647 mm
Overall width	450 mm
Overall height	211 mm
Dimensions (height x width x depth)	211 x 450 x 647 mm

Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-11%

Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful	5 %
life 50,000 h	
Control gear failure rate at median useful	10 %
life 100,000 h	
Lumen maintenance at median useful	L85
life* 50,000 h	
Lumen maintenance at median useful	L70
life* 100,000 h	

Application Conditions	
Performance ambient temperature Tq	25 ℃
Maximum dim level	10%
Suitable for random switching	Yes

Product Data

Floduct Data	
Order product name	BY471X GRN250S/840 HRO PC ACW SI
Full product name	BY471X GRN250S/840 HRO PC ACW SI
Full EOC	871869632155300
Order code	32155300
Material no. (12 NC)	910930205914
SAP numerator – quantity per pack	1
EAN/UPC — Product/Case	8718696321553
Numerator – packs per outer box	1
EAN/UPC - Case	8718696321553

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	9.6 A
Inrush time	2.3 ms
Power Consumption	165 W
Power Factor (Fraction)	0.9
Connection	External connector
Cable	Cable 0.5 m with cable connector 3-pole
Number of products on MCB of 16 A type	6

в

Temperature

Ambient temperature range

Controls and Dimming


Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing material	Aluminium

-20 to +45 °C

The ability material	/ terriniterini
Reflector material	-
Optic material	Acrylate
Optical cover/lens material	Polycarbonate
Fixation material	Stainless steel
Housing Colour	Silver

GentleSpace Green Warehouse system

Dimensional drawing





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, April 29 - data subject to change