



# GentleSpace GreenWarehouse

## BY471X GRN170S/840 HRO PC ACW WH

GentleSpace GreenWarehouse, LED GreenLine system flux 17000 lm, 840 neutral white, High-rack optic, Polycarbonate bowl/cover, ActiLume wireless, White

This dedicated system makes it easy for warehouse developers and facility managers to achieve maximum energy savings. It seamlessly integrates state-of-the-art LED lighting with an easy-to-use and reliable networked control solution. When the situation on the work floor changes, settings such as dimming levels and timing can be changed wirelessly by the end-users themselves. Luminaires can be combined in groups across the layout, and re-zoning them does not require a hardware change, thus minimizing commissioning costs. The system delivers savings over and above the actual efficiency of the LEDs and is future-proof. Easy to understand, easy to design-in, and easy to use, the GreenWarehouse is simplicity itself.

### Product data

General Information		
Lamp family code	GRN170S [LED GreenLine system flux 17000 lm]	maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.
Light source replaceable	Yes	
Number of gear units	1 unit	
Driver included	Yes	
Remarks	* -Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen	
		Product family code
		BY471X [GentleSpace GreenWarehouse]
		Lighting Technology
		LED
		Embedded control
		ActiLume wireless
		CE mark
		Yes
		Warranty period
		5 years
		Flammability mark
		For mounting on easily flammable surfaces
		ENEC mark
		ENEC mark

# GentleSpace GreenWarehouse

Glow-wire test	Temperature 650 °C, duration 5 s
EU RoHS compliant	Yes

## Light Technical

Luminous Flux	17,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	153 lm/W
Color rendering index (CRI)	≥80
Number of light sources	12
Beam angle of light source	114 degree(s)
Light source color	840 neutral white
Optic type	High-rack optic
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	16° x 47°
Unified glare rating CEN	Not applicable

## Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	4.8 A
Inrush time	2.3 ms
Power Consumption	111 W
Power Factor (Fraction)	0.9
Connection	External connector
Cable	Cable 0.5 m with cable connector 3-pole
Number of products on MCB of 16 A type B	12

## Temperature

Ambient temperature range	-20 to +45 °C
---------------------------	---------------

## Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	-
Constant light output	No

## Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Acrylate
Optical cover material	Polycarbonate
Fixation material	Stainless steel
Housing Color	White

Optical cover finish	Clear
Overall length	647 mm
Overall width	450 mm
Overall height	211 mm
Dimensions (Height x Width x Depth)	211 x 450 x 647 mm

## Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-11%

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 50000 h	L85
Lumen maintenance at median useful life* 100000 h	L70

## Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	10%
Suitable for random switching	Yes

## Product Data

Order product name	BY471X GRN170S/840 HRO PC ACW WH
Full product name	BY471X GRN170S/840 HRO PC ACW WH
Full product code	871869632175100
Order code	32175100
Material Nr. (12NC)	910930205934
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696321751
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696321751

### Dimensional drawing

