



GentleSpace gen2

BY470P GRN130S/840 PSD WB GC BR SI

GentleSpace 2, LED GreenLine system flux 13000 lm, Power supply unit with DALI interface, Wide beam, Clear glass, Silver

With the introduction of the GentleSpace LED luminaire in 2011, Philips achieved a breakthrough in high-bay lighting, offering a huge reduction in power consumption, a long service life and an innovative design. Now, with GentleSpace gen2, Philips is setting a new standard in the market, with an improved total cost of ownership, even in extreme conditions. In addition, a high diversity of options are available to ensure an ideal solution for your application like optics, coatings and enabling the use of a central emergency grid (PSED).

Product data

General Information		Lighting Technology	
Lamp family code	GRN130S [LED GreenLine system flux 13000 lm]	Embedded control	-
Cap-Base	- [-]	CE mark	Yes
Light source replaceable	Yes	Warranty period	5 years
Number of gear units	1 unit	Flammability mark	For mounting on easily flammable surfaces
Gear	EB [Electronic]	ENEC mark	ENEC mark
Driver included	Yes	Glow-wire test	Temperature 850 °C, duration 5 s
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	EU RoHS compliant	Yes
Service tag	Yes	Light Technical	
Product family code	BY470P [GentleSpace 2]	Luminous Flux	13,000 lm
		Correlated Color Temperature (Nom)	4000 K
		Luminous Efficacy (rated) (Nom)	149 lm/W
		Color rendering index (CRI)	≥80
		Number of light sources	8
		Beam angle of light source	114 degree(s)

GentleSpace gen2

Light source color	840 neutral white
Optic type	Wide beam
Optical cover type	Clear glass
Luminaire light beam spread	42° x 44°
Unified glare rating CEN	25

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	4.8 A
Inrush time	2.3 ms
Power Consumption	87 W
Power Factor (Fraction)	0.9
Connection	External connector
Cable	Cord with plug Wieland/Adels compatible 5-pole
Number of products on MCB of 16 A type B	12

Temperature

Ambient temperature range	-30 to +45 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Acrylate
Optical cover material	Glass
Fixation material	Steel
Housing Color	Silver
Optical cover finish	Clear
Overall length	450 mm
Overall width	350 mm
Overall height	130 mm

Dimensions (Height x Width x Depth)	130 x 350 x 450 mm
-------------------------------------	--------------------

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-11%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 50000 h	L85
Lumen maintenance at median useful life* 100000 h	L70

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	10%
Suitable for random switching	No

Product Data

Order product name	BY470P GRN130S/840 PSD WB GC BR SI
Full product name	BY470P GRN130S/840 PSD WB GC BR SI
Full product code	871869632184300
Order code	32184300
Material Nr. (12NC)	910930205943
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696321843
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696321843

GentleSpace gen2

Dimensional drawing

