



# GentleSpace gen2

## BY471P GRN250S/840 PSD HRO PC BR SI

GentleSpace 2, LED GreenLine system flux 25000 lm, 840 neutral white, Power supply unit with DALI interface, High-rack optic, Polycarbonate bowl/cover, Silver

With the introduction of the GentleSpace LED luminaire in 2011, Philips achieved a breakthrough in high-bay lighting, offering a huge reduction in power consumption, a long service life and an innovative design. Now, with GentleSpace gen2, Philips continues to improve even further: an improved total cost of ownership, even in extreme conditions with the the GS-2 Xtreme version, which can be used up to +60 °C or 100,000 hrs of lifetime (L80), both ensured by an integrated over-heat protection. In addition, a wide variety of options – e.g. optics, coatings, mounting possibilities, cover materials and suitable for explosive zones 2/22 – are available to ensure an ideal solution for your application. Additionally, the GentleSpace gen2 can be equipped for use in a central emergency grid (PSED).

### Product data

General Information		
Lamp family code	GRN250S [LED GreenLine system flux 25000 lm]	maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.
Cap-Base	- [-]	
Light source replaceable	Yes	
Number of gear units	2 units	
Gear	EB [Electronic]	
Driver included	Yes	
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen	
Service tag	Yes	
Product family code	BY471P [GentleSpace 2]	
Lighting Technology	LED	
Glow-wire test	Temperature 850 °C, duration 5 s	
Flammability mark	For mounting on easily flammable surfaces	
CE mark	Yes	
ENEC mark	ENEC mark	
Warranty period	5 years	
EU RoHS compliant	Yes	

## GentleSpace gen2

Embedded control	-
------------------	---

### Light Technical

Luminous Flux	25,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	152 lm/W
Color rendering index (CRI)	≥80
Number of light sources	16
Beam angle of light source	114 degree(s)
Light source color	840 neutral white
Optic type	High-rack optic
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	16° x 47°
Unified glare rating CEN	Not applicable

### Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	9.6 A
Inrush time	2.3 ms
Power Consumption	164 W
Power Factor (Fraction)	0.9
Connection	External connector
Cable	Cord with plug Wieland/Adels compatible 5-pole
Number of products on MCB of 16 A type B	6

### Temperature

Ambient temperature range	-30 to +45 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

### Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Acrylate
Optical cover material	Polymethyl methacrylate
Fixation material	Steel
Housing Color	Silver

Optical cover finish	Clear
Overall length	600 mm
Overall width	450 mm
Overall height	150 mm
Dimensions (Height x Width x Depth)	150 x 450 x 600 mm

### Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-11%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 50000 h	L85
Lumen maintenance at median useful life* 100000 h	L70

### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	10%
Suitable for random switching	No

### Product Data

Order product name	BY471P GRN250S/840 PSD HRO PC BR SI
Full product name	BY471P GRN250S/840 PSD HRO PC BR SI
Full product code	871869632219200
Order code	910930205978
Material Nr. (12NC)	910930205978
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696322192
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696322192

## GentleSpace gen2

### Dimensional drawing

