



GentleSpace gen2

BY471P GRN250S/840 PSD MB AC BR SI

GentleSpace 2 - LED GreenLine system flux 25000 lm - 840 neutral white - Power supply unit with DALI interface - Medium beam - Acrylic bowl/cover - Bracket - Silver

With the introduction of the GentleSpace LED luminaire in 2011, Philips achieved a breakthrough in high-bay lighting, offering a huge reduction in power consumption, a long service life and an innovative design. Now, with GentleSpace gen2, Philips is setting a new standard in the market, with an improved total cost of ownership, even in extreme conditions. In addition, a high diversity of options are available to ensure an ideal solution for your application like optics, coatings and enabling the use of a central emergency grid (PSED).

Product data

| General Information | | Embedded control | No [-] |
|-------------------------------|-----------------------------------------------|-----------------------------|------------------------------------------------|
| Number of light sources | 16 [16 pcs] | Control interface | DALI |
| Lamp family code | GRN250S [LED GreenLine system flux 25000 lm] | Connection | External connector |
| Beam angle of light source | 114 ° | Cable | Cord with plug Wieland/Adels compatible 5-pole |
| Light source colour | 840 neutral white | Protection class IEC | Safety class I |
| Cap base | - [-] | Mounting | BR [Bracket] |
| Light source replaceable | Yes | Coating | - |
| Number of gear units | 2 units | Glow-wire test | Temperature 650 °C, duration 5 s |
| Gear | EB [Electronic] | Flammability mark | D [For mounting on easily flammable surfaces] |
| Driver/power unit/transformer | PSD [Power supply unit with DALI interface] | CE mark | CE mark |
| Driver included | Yes | ENEC mark | ENEC mark |
| Optic type | MB [Medium beam] | Ball impact resistance mark | - |
| Optical cover/lens type | AC [Acrylic bowl/cover] | Design award-winner marking | Design Award Winner 2014 |
| Luminaire light beam spread | 40° x 40° | | |

GentleSpace gen2

| | |
|---------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Warranty period | 5 years |
| Suspension accessories | No [-] |
| Remarks | *-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore the median useful life (B50) value also represents the B10 value. |
| Constant light output | No |
| Number of products on MCB | 6 |
| RoHS mark | RoHS mark |
| Product Family Code | BY471P [GentleSpace 2] |
| Unified glare rating CEN | 25 |

Operating and Electrical

| | |
|------------------------|----------------|
| Input voltage | 220-240 V |
| Input frequency | 50 to 60 Hz |
| Control signal voltage | 0-16 V DC DALI |
| Inrush current | 9.6 A |
| Inrush time | 2.3 ms |
| Power factor (min.) | 0.9 |

Controls and Dimming

| | |
|----------|-----|
| Dimmable | Yes |
|----------|-----|

Mechanical and Housing

| | |
|-----------------------------|-----------|
| Housing material | Aluminium |
| Reflector material | - |
| Optic material | Acrylate |
| Optical cover/lens material | Acrylate |
| Gear tray material | Steel |
| Fixation material | Steel |
| Optical cover/lens finish | Clear |
| Overall length | 600 mm |
| Overall width | 450 mm |
| Overall height | 150 mm |
| Colour | Silver |

Approval and Application

| | |
|-------------------------|------------------------------------------------|
| Ingress protection code | IP65 [Dust penetration-protected, jet-proof] |
|-------------------------|------------------------------------------------|

| | |
|------------------------------|-------------------------|
| Mech. impact protection code | IK07 [2 J reinforced] |
|------------------------------|-------------------------|

Initial Performance (IEC Compliant)

| | |
|--------------------------------|----------------------|
| Initial luminous flux | 25000 lm |
| Luminous flux tolerance | +/-7% |
| Initial LED luminaire efficacy | 152 lm/W |
| Init. Corr. colour temperature | 4000 K |
| Init. colour rendering index | ≥80 |
| Initial chromaticity | (0.38, 0.38) SDCM <3 |
| Initial input power | 164 W |
| Power consumption tolerance | +/-11% |

Over Time Performance (IEC Compliant)

| | |
|----------------------------------------------------------|------|
| Control gear failure rate at median useful life 50000 h | 5 % |
| Control gear failure rate at median useful life 100000 h | 10 % |
| Lumen maintenance at median useful life* 50000 h | L85 |
| Lumen maintenance at median useful life* 100000 h | L70 |

Application Conditions

| | |
|------------------------------------|---------------|
| Ambient temperature range | -30 to +45 °C |
| Performance ambient temperature Tq | 25 °C |
| Maximum dimming level | 10% |
| Suitable for random switching | No |

Product Data

| | |
|---------------------------------|------------------------------------|
| Full product code | 871869632225300 |
| Order product name | BY471P GRN250S/840 PSD MB AC BR SI |
| EAN/UPC – product | 8718696322253 |
| Order code | 32225300 |
| Numerator – quantity per pack | 1 |
| Numerator – packs per outer box | 1 |
| Material no. (12NC) | 910930205984 |
| Net weight (piece) | 17.400 kg |

GentleSpace gen2

Dimensional drawing



GentleSpace gen2 BY470P-BY473P

