



GentleSpace gen2

BY470P GRN130S/840 PSD HRO GC BR SI

GentleSpace 2, LED GreenLine system flux 13000 lm, 840 neutral white, Power supply unit with DALI interface, High-rack optic, Clear glass, Silver

With the introduction of the GentleSpace LED luminaire in 2011, Philips achieved a breakthrough in high-bay lighting, offering a huge reduction in power consumption, a long service life and an innovative design. Now, with GentleSpace gen2, Philips is setting a new standard in the market, with an improved total cost of ownership, even in extreme conditions. In addition, a high diversity of options are available to ensure an ideal solution for your application like optics, coatings and enabling the use of a central emergency grid (PSED).

Product data

General Information		
Lamp family code	GRN130S [LED GreenLine system flux 13000 lm]	useful life (B50) value also represents the B10 value.
Cap base	- [-]	
Light source replaceable	Yes	
Number of gear units	Unit	
Gear	EB [Electronic]	
Driver included	Yes	
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median	
Light Technical		
Luminous Flux	13,000 lm	
Correlated Colour Temperature	4000 K	
Product family code	BY470P [GentleSpace 2]	
Lighting Technology	LED	
Embedded control	-	
CE mark	Yes	
Warranty period	5 years	
Flammability mark	For mounting on easily flammable surfaces	
ENEC mark	ENEC mark	
Glow-wire test	Temperature 850 °C, duration 5 s	
EU RoHS compliant	Yes	

GentleSpace gen2

Luminous efficacy (rated) (nom.)	149 lm/W
Colour rendering index (CRI)	≥80
Beam angle of light source	114 degree(s)
Light source colour	840 neutral white
Optic type	High-rack optic
Optical cover type	Clear glass
Luminaire light beam spread	16° x 47°
Unified Glare Rating (CEN)	Not applicable

Operating and Electrical

Input Voltage	220–240 V
Line Frequency	50 to 60 Hz
Inrush current	4.8 A
Inrush time	2.3 ms
Power Consumption	87 W
Power Factor (Fraction)	0.9
Connection	External connector
Cable	Cord with plug Wieland/Adels compatible 5-pole
Number of products on MCB of 16 A type B	12

Temperature

Ambient temperature range	-30 to +45 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing material	Aluminium
Reflector material	-
Optic material	Acrylate
Optical cover/lens material	Glass
Fixation material	Steel
Housing Colour	Silver
Optical cover/lens finish	Clear
Overall length	450 mm
Overall width	350 mm

Overall height	130 mm
Dimensions (height x width x depth)	130 x 350 x 450 mm

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-11%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 50,000 h	L85
Lumen maintenance at median useful life* 100,000 h	L70

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	10%
Suitable for random switching	No

Product Data

Order product name	BY470P GRN130S/840 PSD HRO GC BR SI
Full product name	BY470P GRN130S/840 PSD HRO GC BR SI
Full EOC	871869632262800
Order code	32262800
Material no. (12 NC)	910930206022
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696322628
Numerator – packs per outer box	1
EAN/UPC - Case	8718696322628

GentleSpace gen2

Dimensional drawing

