



GentleSpace gen2

BY470P GRN130S/840 PSD HRO PC SI

GentleSpace 2, LED GreenLine system flux 13000 lm, 840 neutral white, Power supply unit with DALI interface, High-rack optic, Polycarbonate bowl/cover, Silver

With the introduction of the GentleSpace LED luminaire in 2011, Philips achieved a breakthrough in high-bay lighting, offering a huge reduction in power consumption, a long service life and an innovative design. Now, with GentleSpace gen2, Philips is setting a new standard in the market, with an improved total cost of ownership, even in extreme conditions. In addition, a high diversity of options are available to ensure an ideal solution for your application like optics, coatings and enabling the use of a central emergency grid (PSED).

Product data

General Information		Service tag	
Lamp family code	GRN130S [LED GreenLine system flux 13000 lm]	Service tag	Yes
Cap-Base	- [-]	Product family code	BY470P [GentleSpace 2]
Light source replaceable	Yes	Lighting Technology	LED
Number of gear units	1 unit	Embedded control	-
Gear	EB [Electronic]	CE mark	Yes
Driver included	Yes	Warranty period	5 years
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Flammability mark	For mounting on easily flammable surfaces
		ENEC mark	ENEC mark
		Glow-wire test	Temperature 850 °C, duration 5 s
		EU RoHS compliant	Yes
		Light Technical	
		Luminous Flux	13,000 lm
		Correlated Color Temperature (Nom)	4000 K
		Luminous Efficacy (rated) (Nom)	149 lm/W

GentleSpace gen2

Color rendering index (CRI)	≥80
Number of light sources	8
Beam angle of light source	114 degree(s)
Light source color	840 neutral white
Optic type	High-rack optic
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	16° x 47°
Unified glare rating CEN	Not applicable

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	4.8 A
Inrush time	2.3 ms
Power Consumption	87 W
Power Factor (Fraction)	0.9
Connection	External connector
Cable	Cord with plug Wieland/Adels compatible 5-pole
Number of products on MCB of 16 A type B	12

Temperature

Ambient temperature range	-30 to +45 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Acrylate
Optical cover material	Polymethyl methacrylate
Fixation material	Stainless steel
Housing Color	Silver
Optical cover finish	Clear
Overall length	450 mm
Overall width	350 mm

Overall height	130 mm
Dimensions (Height x Width x Depth)	130 x 350 x 450 mm

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-11%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 50000 h	L85
Lumen maintenance at median useful life* 100000 h	L70

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	10%
Suitable for random switching	No

Product Data

Order product name	BY470P GRN130S/840 PSD HRO PC SI
Full product name	BY470P GRN130S/840 PSD HRO PC SI
Full product code	871869632269700
Order code	32269700
Material Nr. (12NC)	910930206029
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696322697
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696322697

GentleSpace gen2

Dimensional drawing

