



# GentleSpace gen2

BY471P GRN170S/840 PSD-CLO WB GC BR SI S

GentleSpace 2, LED GreenLine system flux 17000 lm, 840 neutral white, Power supply unit with DALI interface and constant light output, Wide beam, Silver, Swimming pool protected coating

With the introduction of the GentleSpace LED luminaire in 2011, Philips achieved a breakthrough in high-bay lighting, offering a huge reduction in power consumption, a long service life and an innovative design. Now, with GentleSpace gen2, Philips continues to improve even further: an improved total cost of ownership, even in extreme conditions with the the GS-2 Xtreme version, which can be used up to +60 °C or 100,000 hrs of lifetime (L80), both ensured by an integrated over-heat protection. In addition, a wide variety of options – e.g. optics, coatings, mounting possibilities, cover materials and suitable for explosive zones 2/22 – are available to ensure an ideal solution for your application. Additionally, the GentleSpace gen2 can be equipped for use in a central emergency grid (PSED).

## Product data

General Information	
Lamp family code	GRN170S [LED GreenLine system flux 17000 lm]
Cap-Base	- [-]
Light source replaceable	Yes
Number of gear units	1 unit
Gear	EB [Electronic]
Driver included	Yes
Remarks	* -Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there

	is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.
Service tag	Yes
Product family code	BY471P [GentleSpace 2]
Lighting Technology	LED
Glow-wire test	Temperature 850 °C, duration 5 s
Flammability mark	For mounting on easily flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark

## GentleSpace gen2

Warranty period	5 years
EU RoHS compliant	Yes
Embedded control	-

### Light Technical

Luminous Flux	17,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	155 lm/W
Color rendering index (CRI)	≥80
Number of light sources	12
Beam angle of light source	114 degree(s)
Light source color	840 neutral white
Optic type	Wide beam
Optical cover type	Clear glass
Luminaire light beam spread	44° x 42°
Unified glare rating CEN	25

### Operating and Electrical

Input Voltage	220–240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	88 W
Average CLO power consumption	99 W
Inrush current	4.8 A
Inrush time	2.3 ms
Power Consumption	110 W
Power Factor (Fraction)	0.9
Connection	External connector
Cable	Cord with plug Wieland/Adels compatible 5-pole
Number of products on MCB of 16 A type B	12

### Temperature

Ambient temperature range	-30 to +45 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface and constant light output
Control interface	DALI
Constant light output	Programmable

### Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Acrylate
Optical cover material	Glass

Fixation material	Steel
Housing Color	Silver
Optical cover finish	Clear
Overall length	600 mm
Overall width	450 mm
Overall height	150 mm
Dimensions (Height x Width x Depth)	150 x 450 x 600 mm

### Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-11%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 50000 h	L85
Lumen maintenance at median useful life* 100000 h	L70

### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	10%
Suitable for random switching	No

### Product Data

Order product name	BY471P GRN170S/840 PSD-CLO WB GC BR SI S
Full product name	BY471P GRN170S/840 PSD-CLO WB GC BR SI S
Full product code	871869632298700
Order code	910930206058
Material Nr. (12NC)	910930206058
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696322987
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696322987

## GentleSpace gen2

### Dimensional drawing

