



FCC110/120 XCC120

FCC110 PL-S/2P9W/827 230V II

SECURITY 110, PL-S 2 Pin, 9 W

FCC110/120 and XCC120 (ceiling-mounted) are attractive, low-energy luminaires for all-night security and amenity lighting. The high-reflectance white plate and translucent bowl with prismatic control produce excellent light distribution for low-level lighting of walls, corridors and surroundings.

Product data

General Information	
Lamp family code	PL-S/2P [PL-S 2 Pin]
Gear	CONV [Conventional]
Photocell	-
Product family code	FCC110 [SECURITY 110]
CE mark	Yes
Flammability mark	For mounting on normally flammable surfaces
Light Technical	
Number of light sources	1
Light source color	827 warm white
Operating and Electrical	
Input Voltage	230 V
Power Consumption	9 W
Mechanical and Housing	
Housing Color	White

Approval and Application	
Ingress protection code	IP54 [Dust accumulation-protected, splash-proof]
Protection class IEC	Safety class II
Product Data	
Order product name	FCC110 PL-S/2P9W/827 230V II
Full product name	FCC110 PL-S/2P9W/827 230V II
Full product code	871155900028299
Order code	911120021012
Material Nr. (12NC)	911120021012
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559000282
Numerator - Packs per outer box	4
EAN/UPC - Case	8711559000350

FCC110/120 XCC120

Dimensional drawing

