



# Tango MMF283

## MMF283 MHN-TD150W 240V-50Hz A

MHN-TD, 150 W, Asymmetrical

Compact, sturdy floodlight complete with integral gear, particularly suited for surface lighting using metal halide or high-pressure sodium lamps. All-weather construction designed for simple cleaning and speedy servicing.

### Product data

General Information	
Lamp family code	MHN-TD
Cap-Base	- [-]
Gear	CONV [Conventional]
Light Technical	
Number of light sources	1
Optic type outdoor	Asymmetrical
Operating and Electrical	
Input Voltage	240 V
Line Frequency	50 Hz
Power Consumption	150 W
Mechanical and Housing	
Housing Color	-

Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Product Data	
Order product name	MMF283 MHN-TD150W 240V-50Hz A
Full product name	MMF283 MHN-TD150W 240V-50Hz A
Full product code	911400419680
Order code	911400419680
Material Nr. (12NC)	911400419680
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Tango MMF283

Dimensional drawing

