



TMS011

TMS011 2xTL-D36W HFS 220V 50Hz

2, MASTER TL-D, 36 W, Electronic standard, 50 Hz

An indoor luminaire in single and twin fluorescent lamp versions for general lighting. The range is available with TLD 18W, 36W or 58W lamps for surface-mounted applications. The luminaires can be suspended or direct ceiling mounted. A range of attractive attachments is also available.

Product data

General Information	
Lamp family code	TL-D [MASTER TL-D]
Gear	EBS [Electronic standard]
Light Technical	
Number of light sources	2
Optic type	-
Optical cover type	-
Operating and Electrical	
Line Frequency	50 Hz
Power Consumption	36 W
Approval and Application	
Ingress protection code	IP20 [Finger-protected]

Protection class IEC	Safety class I
Product Data	
Order product name	TMS011 2xTL-D36W HFS 220V 50Hz
Full product name	TMS011 2xTL-D36W HFS 220V 50Hz
Full product code	911400865780
Order code	911400865780
Material Nr. (12NC)	911400865780
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6

TMS011

Dimensional drawing

